

2024年4月

お得意先様 各位

アズワン株式会社
営業本部

価格改定のご案内

拝啓 貴社益々ご清栄こととお慶び申し上げます。平素は格別なるご高配を賜り、厚く御礼申し上げます。

掲題の件、原材料コストや輸送費の上昇等により、誠に不本意ではございますが、
一部の商品につき、2024年5月1日付で価格改定を実施させて頂きたく、ご案内申し上げます。

弊社といたしましても、ユーザー様、販売店様へご迷惑の掛からぬよう企業努力で対応して参りましたが、
弊社の努力だけでは吸収しがたい状況となつてきております。

ユーザー様、販売店様にはご迷惑をお掛けいたしますが、諸般の事情をご賢察頂き、
ご理解賜りますようお願い申し上げます。

敬具

価格改定表

研究用総合機器カタログ2023
サンクアスト産業用研究機器カタログ2023
ナビス看護・医療用品総合カタログ2024
サニーフーズカタログ2024
研究設備カタログ2024
アズピュア クリーン環境・静電気対策カタログ2023
アズツール 生産現場向け副資材カタログ2021
介護・医療用品総合カタログ ナビ助2023
感染症対策用品パンフレット
PluSmile+ウェルビーイング対策用品パンフレット
サイエンスカタログ2024-2025

2024年5月1日

 **アズワン株式会社**

品番	商品名	旧価格	新価格	研究用総合 機軸2023 頁	サンクアス ト 2023 頁	ナビス2024 頁	サニーフーズ 2024 頁	数値2024 頁	アズビエア 2023 頁	アズツール 2021 頁	ナビ助2023 頁	産産産産産 用品/パンフ 頁	ウェルビー イング/パン フ 頁	サイエンス カタログ 頁
2-320-09	定性濾紙 角形No.4 46×57cm 100枚入 1004-917	28,800	29,200	1637	1637									
2-321-01	定性濾紙 円形No.5 5.5cm 100枚入 1005-055	1,290	1,320	1637	1637									
2-321-02	定性濾紙 円形No.5 7.0cm 100枚入 1005-070	1,790	1,830	1637	1637									
2-321-03	定性濾紙 円形No.5 9.0cm 100枚入 1005-090	1,990	2,030	1637	1637									
2-321-04	定性濾紙 円形No.5 11.0cm 100枚入 1005-110	2,360	2,410	1637	1637									
2-321-05	定性濾紙 円形No.5 12.5cm 100枚入 1005-125	2,750	2,800	1637	1637									
2-321-06	定性濾紙 円形No.5 15.0cm 100枚入 1005-150	4,100	4,180	1637	1637									
2-321-07	定性濾紙 円形No.5 18.5cm 100枚入 1005-185	5,710	5,820	1637	1637									
2-321-08	定性濾紙 円形No.5 24.0cm 100枚入 1005-240	8,910	9,090	1637	1637									
2-322-02	定性濾紙 円形No.6 7.0cm 100枚入 1006-070	1,530	1,560	1637	1637									
2-322-03	定性濾紙 円形No.6 9.0cm 100枚入 1006-090	1,790	1,830	1637	1637									
2-322-04	定性濾紙 円形No.6 11.0cm 100枚入 1006-110	2,230	2,270	1637	1637									
2-322-05	定性濾紙 円形No.6 12.5cm 100枚入 1006-125	2,610	2,660	1637	1637									
2-322-06	定性濾紙 円形No.6 15.0cm 100枚入 1006-150	3,840	3,920	1637	1637									
2-322-07	定性濾紙 円形No.6 18.5cm 100枚入 1006-185	5,340	5,450	1637	1637									
2-322-08	定性濾紙 円形No.6 24.0cm 100枚入 1006-240	6,940	7,080	1637	1637									
2-323-01	定量濾紙 円形No.40 5.5cm 100枚入 1440-055	2,170	2,210	1637	1637									
2-323-02	定量濾紙 円形No.40 7.0cm 100枚入 1440-070	2,730	2,780	1637	1637									
2-323-03	定量濾紙 円形No.40 9.0cm 100枚入 1440-090	2,860	2,920	1637	1637									
2-323-04	定量濾紙 円形No.40 11.0cm 100枚入 1440-110	3,530	3,600	1637	1637									
2-323-05	定量濾紙 円形No.40 12.5cm 100枚入 1440-125	4,720	4,810	1637	1637									
2-323-06	定量濾紙 円形No.40 15.0cm 100枚入 1440-150	6,440	6,570	1637	1637									
2-323-07	定量濾紙 円形No.40 18.5cm 100枚入 1440-185	9,530	9,720	1637	1637									
2-323-08	定量濾紙 円形No.40 24.0cm 100枚入 1440-240	15,070	15,370	1637	1637									
2-323-09	定量濾紙 角形No.40 46×57cm 100枚入 1440-917	58,900	60,100	1637	1637									
2-324-01	定量濾紙 円形No.41 5.5cm 100枚入 1441-055	2,170	2,210	1637	1637									
2-324-02	定量濾紙 円形No.41 7.0cm 100枚入 1441-070	2,730	2,780	1637	1637									
2-324-03	定量濾紙 円形No.41 9.0cm 100枚入 1441-090	2,860	2,920	1637	1637									
2-324-04	定量濾紙 円形No.41 11.0cm 100枚入 1441-110	3,530	3,600	1637	1637									
2-324-05	定量濾紙 円形No.41 12.5cm 100枚入 1441-125	4,720	4,810	1637	1637									
2-324-06	定量濾紙 円形No.41 15.0cm 100枚入 1441-150	6,440	6,570	1637	1637									
2-324-07	定量濾紙 円形No.41 18.5cm 100枚入 1441-185	9,530	9,720	1637	1637									
2-324-08	定量濾紙 円形No.41 24.0cm 100枚入 1441-240	15,070	15,370	1637	1637									
2-324-09	定量濾紙 角形No.41 46×57cm 100枚入 1441-917	58,900	60,100	1637	1637									
2-325-01	定量濾紙 円形No.42 5.5cm 100枚入 1442-055	2,170	2,210	1637	1637									
2-325-02	定量濾紙 円形No.42 7.0cm 100枚入 1442-070	2,730	2,780	1637	1637									
2-325-03	定量濾紙 円形No.42 9.0cm 100枚入 1442-090	2,860	2,920	1637	1637									
2-325-04	定量濾紙 円形No.42 11.0cm 100枚入 1442-110	3,530	3,600	1637	1637									
2-325-05	定量濾紙 円形No.42 12.5cm 100枚入 1442-125	4,720	4,810	1637	1637									
2-325-06	定量濾紙 円形No.42 15.0cm 100枚入 1442-150	6,440	6,570	1637	1637									
2-325-07	定量濾紙 円形No.42 18.5cm 100枚入 1442-185	9,530	9,720	1637	1637									
2-325-08	定量濾紙 円形No.42 24.0cm 100枚入 1442-240	15,070	15,370	1637	1637									
2-325-09	定量濾紙 角形No.42 46×57cm 100枚入 1442-917	56,400	57,500	1637	1637									
2-326-02	定量濾紙 円形No.44 7.0cm 100枚入 1444-070	2,730	2,780	1637	1637									
2-326-03	定量濾紙 円形No.44 9.0cm 100枚入 1444-090	2,860	2,920	1637	1637									
2-326-04	定量濾紙 円形No.44 11.0cm 100枚入 1444-110	3,530	3,600	1637	1637									
2-326-05	定量濾紙 円形No.44 12.5cm 100枚入 1444-125	4,720	4,810	1637	1637									
2-326-06	定量濾紙 円形No.44 15.0cm 100枚入 1444-150	6,440	6,570	1637	1637									
2-326-07	定量濾紙 円形No.44 18.5cm 100枚入 1444-185	9,530	9,720	1637	1637									
2-326-08	定量濾紙 円形No.44 24.0cm 100枚入 1444-240	16,280	16,610	1637	1637									
2-327-01	定量濾紙 円形No.50 5.5cm 100枚入 1450-055	1,900	1,940	1637	1637									
2-327-02	定量濾紙 円形No.50 7.0cm 100枚入 1450-070	2,430	2,480	1637	1637									
2-327-03	定量濾紙 円形No.50 9.0cm 100枚入 1450-090	2,610	2,660	1637	1637									
2-327-04	定量濾紙 円形No.50 11.0cm 100枚入 1450-110	3,340	3,410	1637	1637									
2-327-05	定量濾紙 円形No.50 12.5cm 100枚入 1450-125	4,210	4,290	1637	1637									
2-327-06	定量濾紙 円形No.50 15.0cm 100枚入 1450-150	5,670	5,780	1637	1637									
2-327-07	定量濾紙 円形No.50 18.5cm 100枚入 1450-185	8,060	8,220	1637	1637									
2-327-08	定量濾紙 円形No.50 24.0cm 100枚入 1450-240	13,310	13,580	1637	1637									
2-327-09	定量濾紙 角形No.50 46×57cm 100枚入 1450-917	59,100	60,300	1637	1637									
2-328-01	定量濾紙 円形No.540 5.5cm 100枚入 1540-055	2,320	2,370	1637	1637									
2-328-03	定量濾紙 円形No.540 9.0cm 100枚入 1540-090	2,860	2,920	1637	1637									
2-328-04	定量濾紙 円形No.540 11.0cm 100枚入 1540-110	3,530	3,600	1637	1637									
2-328-05	定量濾紙 円形No.540 12.5cm 100枚入 1540-125	4,720	4,810	1637	1637									
2-328-06	定量濾紙 円形No.540 15.0cm 100枚入 1540-150	6,440	6,570	1637	1637									
2-328-07	定量濾紙 円形No.540 18.5cm 100枚入 1540-185	9,530	9,720	1637	1637									
2-328-08	定量濾紙 円形No.540 24.0cm 100枚入 1540-240	15,070	15,370	1637	1637									
2-329-01	ガラス繊維円形濾紙GF/A 2.1cm 100枚入 1820-021	2,380	2,430	1638	1638									
2-329-02	ガラス繊維円形濾紙GF/A 2.4cm 100枚入 1820-024	2,630	2,680	1638	1638									
2-329-03	ガラス繊維円形濾紙GF/A 2.5cm 100枚入 1820-025	2,630	2,680	1638	1638									
2-329-04	ガラス繊維円形濾紙GF/A 3.7cm 100枚入 1820-037	3,860	3,940	1638	1638									
2-329-05	ガラス繊維円形濾紙GF/A 4.25cm 100枚入 1820-042	4,240	4,320	1638	1638									
2-329-06	ガラス繊維円形濾紙GF/A 4.7cm 100枚入 1820-047	4,370	4,460	1638	1638									
2-329-07	ガラス繊維円形濾紙GF/A 5.5cm 100枚入 1820-055	5,130	5,230	1638	1638									
2-329-08	ガラス繊維円形濾紙GF/A 6.0cm 100枚入 1820-060	5,370	5,480	1638	1638									
2-329-09	ガラス繊維円形濾紙GF/A 7.0cm 100枚入 1820-070	5,870	5,990	1638	1638									
2-329-10	ガラス繊維円形濾紙GF/A 9.0cm 100枚入 1820-090	6,880	7,020	1638	1638									
2-329-11	ガラス繊維円形濾紙GF/A 11.0cm 100枚入 1820-110	10,100	10,300	1638	1638									
2-329-12	ガラス繊維円形濾紙GF/A 12.5cm 100枚入 1820-125	12,650	12,900	1638	1638									
2-329-13	ガラス繊維円形濾紙GF/A 15.0cm 100枚入 1820-150	17,490	17,840	1638	1638									
2-329-14	ガラス繊維角形濾紙GF/A 46×57cm 25枚入 1820-915	40,000	40,800	1638	1638									
2-330-01	ガラス繊維円形濾紙GF/B 2.1cm 100枚入 1821-021	3,620	3,690	1638	1638									
2-330-02	ガラス繊維円形濾紙GF/B 2.4cm 100枚入 1821-024	4,120	4,200	1638	1638									
2-330-03	ガラス繊維円形濾紙GF/B 2.5cm 100枚入 1821-025	4,120	4,200	1638	1638									
2-330-04	ガラス繊維円形濾紙GF/B 3.7cm 100枚入 1821-037	6,490	6,620	1638	1638									
2-330-05	ガラス繊維円形濾紙GF/B 4.25cm 100枚入 1821-042	6,730	6,860	1638	1638									
2-330-06	ガラス繊維円形濾紙GF/B 4.7cm 100枚入 1821-047	6,880	7,020	1638	1638									
2-330-07	ガラス繊維円形濾紙GF/B 5.5cm 100枚入 1821-055	9,110	9,290	1638	1638									
2-330-08	ガラス繊維円形濾紙GF/B 6.0cm 100枚入 1821-060	11,440	11,670	1638	1638									
2-330-09	ガラス繊維円形濾紙GF/B 7.0cm 100枚入 1821-070	13,090	13,350	1638	1638									
2-330-10	ガラス繊維円形濾紙GF/B 9.0cm 25枚入 1821-090	4,370	4,460	1638	1638									
2-330-11	ガラス繊維円形濾紙GF/B 11.0cm 25枚入 1821-110	5,870	5,990	1638	1638									
2-330-12	ガラス繊維円形濾紙GF/B 12.5cm 25枚入 1821-125	7,990	8,150	1638	1638									
2-330-13	ガラス繊維円形濾紙GF/B 15.0cm 25枚入 1821-150	10,590	10,800	1638	1638									
2-330-14	ガラス繊維角形濾紙GF/B 46×57cm 25枚入 1821-915	96,000	97,900	1638	1638									
2-331-01	ガラス繊維円形濾紙GF/C 2.1cm 100枚入 1822-021	3,860	3,940	1638	1638									

2024年5月1日より実施

Table with 14 columns: 品番, 商品名, 旧価格, 新価格, 研究用総合機種2023頁, サンクス2023頁, ナビス2024頁, サニラーツ2024頁, 設備2024頁, アズビエア2023頁, アズツール2021頁, ナビ助2023頁, 産地産材専用品/バンフ頁, ウェルビーイング/バンフ頁, サイエンスカテゴリ頁

品番	商品名	旧価格	新価格	研究用総合 機種2023 頁	サンクスア スト 2023 頁	ナビス2024 頁	サニーフ ーズ2024 頁	設備2024 頁	アズビエ ア 2023 頁	アズツール 2021 頁	ナビ助2023 頁	産学連携 専用パンフ 頁	ウェルビー イングパン フ 頁	サイエンス カタログ 頁
4-1678-05	石英ルツボ(ナンバーリング品) 25mL ナンバー:5 NR4504-205	19,800	22,800	2249	2249									
4-1678-06	石英ルツボ(ナンバーリング品) 25mL ナンバー:6 NR4504-206	19,800	22,800	2249	2249									
4-1678-07	石英ルツボ(ナンバーリング品) 25mL ナンバー:7 NR4504-207	19,800	22,800	2249	2249									
4-1678-08	石英ルツボ(ナンバーリング品) 25mL ナンバー:8 NR4504-208	19,800	22,800	2249	2249									
4-1678-09	石英ルツボ(ナンバーリング品) 25mL ナンバー:9 NR4504-209	19,800	22,800	2249	2249									
4-1678-10	石英ルツボ(ナンバーリング品) 25mL ナンバー:10 NR4504-210	19,800	22,800	2249	2249									
4-1843-01-20	トリプルタイマー 校正証明書付 HS24490M	10,530	10,900	2526	2526									
4-1844-01-20	4チャンネルタイマー 校正証明書付 HS24670	10,300	10,600	2527	2527									
4-1880-01-20	ボタン型温度ロガー 校正証明書付 01-0182	44,800	52,500	635	635									
4-1880-11-20	ボタン型温度ロガー 校正証明書付 01-0180	28,800	32,500	635	635									
4-2035-02	ソフトウェア無線受信機 Airspy HF+ Discovery IM190522001	39,550	56,000	2569	2569									
4-2035-03	ソフトウェア無線受信機 Airspy Mini IM150415001	23,500	32,900	2569	2569									
4-2037-11	ディスプレイ用スコープ 14-241-10A	46,400	53,000	2222	2222									
4-2037-12	ディスプレイ用スコープ 14-241-10B	59,500	67,800	2222	2222									
4-2037-13	ディスプレイ用スコープ 14-241-10C	79,900	91,200	2222	2222									
4-204-01	ハンドカッター(基板用) PC-210	46,900	49,300	3414	3414									
4-204-02	ハンドカッター(基板用) PC-310	89,700	92,100	3414	3414									
4-204-11	ハンドカッター(基板用) PC-210用練習	31,700	35,000	3414	3414									
4-204-12	ハンドカッター(基板用) PC-310用練習	56,100	56,400	3414	3414									
4-2074-01	桌上集塵器 本体 KS240	62,000	68,000	1123	1123									
4-2142-01	静音ステンレス作業台 幅600×奥行450×高さ800mm WS-6045SI	41,000	42,000	1013	1013									
4-2142-02	静音ステンレス作業台 幅750×奥行450×高さ800mm WS-7545SI	43,000	44,000	1013	1013									
4-2142-03	静音ステンレス作業台 幅750×奥行600×高さ800mm WS-7560SI	51,000	53,000	1013	1013									
4-2142-04	静音ステンレス作業台 幅900×奥行450×高さ800mm WS-9045SI	48,000	49,000	1013	1013									
4-2142-05	静音ステンレス作業台 幅900×奥行900×高さ800mm WS-9090SI	71,000	74,000	1013	1013									
4-2142-06	静音ステンレス作業台 幅900×奥行600×高さ800mm WS-9060SI	57,000	59,000	1013	1013									
4-2142-07	静音ステンレス作業台 幅900×奥行750×高さ800mm WS-9075SI	63,000	65,000	1013	1013									
4-2142-08	静音ステンレス作業台 幅1200×奥行450×高さ800mm WS-12045SI	56,000	58,000	1013	1013									
4-2142-09	静音ステンレス作業台 幅1200×奥行600×高さ800mm WS-12060SI	69,000	72,000	1013	1013									
4-2142-10	静音ステンレス作業台 幅1200×奥行750×高さ800mm WS-12075SI	76,000	79,000	1013	1013									
4-2142-11	静音ステンレス作業台 幅1200×奥行900×高さ800mm WS-12090SI	88,000	93,000	1013	1013									
4-2142-12	静音ステンレス作業台 幅1500×奥行600×高さ800mm WS-15060SI	81,000	85,000	1013	1013									
4-2142-13	静音ステンレス作業台 幅1500×奥行750×高さ800mm WS-15075SI	90,000	94,000	1013	1013									
4-2142-14	静音ステンレス作業台 幅1500×奥行900×高さ800mm WS-15090SI	103,000	110,000	1013	1013									
4-2142-15	静音ステンレス作業台 幅1800×奥行600×高さ800mm WS-18060SI	92,000	97,000	1013	1013									
4-2142-16	静音ステンレス作業台 幅1800×奥行750×高さ800mm WS-18075SI	102,000	108,000	1013	1013									
4-2142-17	静音ステンレス作業台 幅1800×奥行900×高さ800mm WS-18090SI	117,000	125,000	1013	1013									
4-2388-01	静電仕様ペーデシキター(マグネットバックリッセン仕様) 574×600×1765mm HDM-SSE	299,000	332,000	1191	1191									
4-2388-02	静電仕様ペーデシキター(マグネットバックリッセン仕様) 1152×600×1765mm HDM-WSE	562,000	613,000	1191	1191									
4-2389-01	静電仕様ガス置換シキター(マグネットバックリッセン仕様) 574×517×1765mm GDM-SSES	244,000	257,000	1194	1194									
4-2389-03	静電仕様ガス置換シキター(マグネットバックリッセン仕様) 574×517×1020mm GDM-BGISES	131,000	137,000	1194	1194									
4-2389-04	静電仕様ガス置換シキター(マグネットバックリッセン仕様) 574×517×1085mm GDM-BG1KSES	134,000	140,000	1194	1194									
4-2389-05	静電仕様ガス置換シキター(マグネットバックリッセン仕様) 574×517×765mm GDM-BG2SES	106,000	113,000	1194	1194									
4-2390-01	ペーデシキター(マグネットバックリッセン仕様) 574×600×1765mm HDM-S	180,000	188,000	1191	1191									
4-2390-02	ペーデシキター(マグネットバックリッセン仕様) 1152×600×1765mm HDM-W	336,000	353,000	1191	1191									
4-2391-01	ガス置換シキター(SUS/マグネットバックリッセン仕様) 574×517×1765mm GDM-SS	164,000	200,000	1193	1193									
4-2391-02	ガス置換シキター(SUS/マグネットバックリッセン仕様) 1152×517×1765mm GDM-WS	305,000	338,000	1193	1193									
4-2392-01	静電仕様ペーデシキター(制電仕様) 574×600×1765mm HD-SS	290,000	335,000	1191	1191									
4-2392-02	静電仕様ペーデシキター(制電仕様) 1152×517×1765mm HD-WSE	566,000	598,000	1191	1191									
4-2424-01	電子回路学習キット(micro:bit) ロジック回路学習ボード MLCTB-BASE	8,150	9,280	2559	2559									
4-2486-07	シヨックコード 50m巻 白 Φ12mm 110452	28,000	32,200	2625	2625									
4-2486-08	シヨックコード 50m巻 白 Φ14mm 110453	39,700	38,000	2625	2625									
4-2834-01	手指消毒剤 カナバス VD 500mL	2,210	2,300			316								
4-2834-02	手指消毒剤 カナバス VD 1000mL	3,600	3,700			316							34	
4-2834-03	手指消毒剤 カナバス VD 5L	13,200	14,400			316							34	
4-3042-01	大型スタンド BS型	37,100	41,700	2183	2183									
4-3203-01	水分計 測定用アルミニウム皿 50枚入 30585411	5,100	5,300	850	850									
4-356-01-20	ペン型pH/導電率計 校正証明書付 MPC70	48,400	49,600	655	655									
4-360-01-20	突き刺し形pH計 校正証明書付 SPH70	57,000	59,000	655	655									
4-361-01-20	平面型pH計 校正証明書付 FPH70	31,000	34,100	655	655									
4-4309-01	防水タイプ台はかり i-D61PW3K1S6JP	240,700	245,600	513	513									
4-4309-02	防水タイプ台はかり i-D61PW6K1S6JP	240,700	245,600	513	513									
4-4309-03	防水タイプ台はかり i-D61PW15K1R6JP	288,100	293,900	513	513									
4-4309-04	防水タイプ台はかり i-D61PW30K1R6JP	288,100	293,900	513	513									
4-4309-05	防水タイプ台はかり i-D61PW60K1L7JP	321,200	327,700	513	513									
4-4309-06	防水タイプ台はかり i-D61PW150K1L7JP	321,200	327,700	513	513									
4-4309-07	防水タイプ台はかり i-D61XWE3K1S6JP	282,600	288,300	513	513									
4-4309-08	防水タイプ台はかり i-D61XWE6K1S6JP	282,600	288,300	513	513									
4-4309-09	防水タイプ台はかり i-D61XWE15K1R6JP	336,700	343,500	513	513									
4-4309-10	防水タイプ台はかり i-D61XWE30K1R6JP	336,700	343,500	513	513									
4-4309-11	防水タイプ台はかり i-D61XWE60K1L7JP	376,400	384,000	513	513									
4-4309-12	防水タイプ台はかり i-D61XWE150K1L7JP	376,400	384,000	513	513									
4-440-01	真空デシキター(VOLTEGA300用) VP型	86,000	95,000	1201	1201									
4-4561-01	電易耐試験機 KTS-A	310,000	328,000	883	883									
4-4561-02	電易耐試験機 KTS-B	330,000	347,000	883	883									
4-485-01-20	M型標準ノギス(校正証明書付) MAC100	8,200	8,400	893	893									528
4-485-02-20	M型標準ノギス(校正証明書付) MAC150	8,200	8,400	893	893									528
4-485-03-20	M型標準ノギス(校正証明書付) MAC200	9,600	9,800	893	893									528
4-485-04-20	M型標準ノギス(校正証明書付) MAC300	14,700	15,200	893	893									528
4-5168-01	FIB試料調整用試料台 SG-002Mo	50,000	55,000	941	941									
4-5168-02	FIB試料調整用試料台 SG-003Ni	48,000	54,000	941	941									
4-5168-03	FIB試料調整用試料台 SG-003Cu	22,800	27,000	941	941									
4-5168-04	FIB試料調整用試料台 SG-003Ti	51,200	56,000	941	941									
4-5316-22	試料保存容器 14-955-114A	35,500	35,900	1828	1828									
4-5316-23	試料保存容器 14-955-115B	18,000	18,600	1828	1828									
4-5316-24	試料保存容器 14-955-116B	18,000	18,700	1828	1828									
4-5316-25	試料保存容器 14-955-117B	20,000	20,300	1828	1828									
4-5316-26	試料保存容器 14-955-118B	33,200	33,800	1828	1828									
4-5316-27	試料保存容器 14-955-119B	24,900	25,200	1828	1828									
4-5316-28	試料保存容器 14-955-120B	17,800	18,000	1828	1828									
4-5316-29	試料保存容器 14-955-121B	11,700	11,900	1828	1828									
4-5581-01	クリーンブース P7-151520	650,000	665,000											
4-5581-02	クリーンブース P7-152020	670,000	685,000											
4-5581-03	クリーンブース P7-152520	800,000	815,000											
4-5581-04	クリーンブース P7-202020	690,000	705,000											
4-5581-05	クリーンブース P7-202520	900,000	915,000											
4-5581-06	クリーンブース P7-203020	950,000	965,000											
4-5581-07	クリーンブース P7-252520	1,080,000	1,095,000											
4-5581-08	クリーンブース P7-253020	1,130,000	1,145,000											
4-5581-09	クリーンブース P7-253520	1,370,000	1,400,000											
4-5581-10	クリーンブース P7-303020	1,270,000												

品番	商品名	旧価格	新価格	研究用総合 機種2023 頁	サンクス 2023 頁	ナビス2024 頁	サニーク 2024 頁	設備2024 頁	アズビエ 2023 頁	アズビエ 2021 頁	ナビ助2023 頁	産産産 用品/パンフ 頁	ウェルビー イング/パン フ 頁	サイエンス カタログ 頁
4-5583-06	クリーンブース P5-203020	1,570,000	1,655,000					340						
4-5583-07	クリーンブース P5-252520	1,830,000	1,929,000					340						
4-5583-08	クリーンブース P5-253020	2,140,000	2,253,000					340						
4-5583-09	クリーンブース P5-253520	2,370,000	2,497,000					340						
4-5583-10	クリーンブース P5-303020	2,280,000	2,407,000					340						
4-5583-11	クリーンブース P5-303520	2,600,000	2,750,000					340						
4-5583-12	クリーンブース P5-353520	3,090,000	3,272,000					340						
4-5584-01	クリーンブース TA5-20	3,700,000	3,780,000					338						
4-5584-02	クリーンブース TA5-25	4,500,000	4,600,000					338						
4-5584-03	クリーンブース TA5-30	5,700,000	5,850,000					338						
4-5585-01	クリーンブース TA6-20	3,000,000	3,010,000					338						
4-5585-02	クリーンブース TA6-25	3,800,000	3,830,000					338						
4-5585-03	クリーンブース TA6-30	4,600,000	4,650,000					338						
4-5586-01	クリーンブース TA7-20	2,950,000	2,960,000					338						
4-5586-02	クリーンブース TA7-25	3,600,000	3,610,000					338						
4-5586-03	クリーンブース TA7-30	4,200,000	4,210,000					338						
4-575-01-20	デジタルマイクロメーター(校正証明書付) DM025	16,700	17,300	897	897									
4-576-01-20	ハンドル付きデジタルハイトゲージ(測定範囲0~300mm) 校正証明書付 DHG300	67,200	69,600	898	898					78				528
4-576-02-20	ハンドル付きデジタルハイトゲージ(測定範囲0~600mm) 校正証明書付 DHG600	123,000	128,000	898	898									
4-745-01	デジタルドライデンシテーター H-Series 574 × 524 × 1765mm TDD-H600SP	286,000	302,000	1165	1165									
4-745-02	デジタルドライデンシテーター H-Series 574 × 524 × 1765mm TDD-H600SS	304,000	320,000	1165	1165									
4-745-03	デジタルドライデンシテーター H-Series 1152 × 524 × 1765mm TDD-H1200WP	540,000	569,000	1165	1165									
4-745-04	デジタルドライデンシテーター H-Series 1152 × 524 × 1765mm TDD-H1200WS	575,000	605,000	1165	1165									
4-745-11	デジタルドライデンシテーター H-Series 574 × 524 × 1765mm TDD-H600SPC	295,000	316,000	1165	1165									
4-745-12	デジタルドライデンシテーター H-Series 574 × 524 × 1765mm TDD-H600SSC	311,000	332,000	1165	1165									
4-745-13	デジタルドライデンシテーター H-Series 1152 × 524 × 1765mm TDD-H1200WPC	548,000	575,000	1165	1165									
4-745-14	デジタルドライデンシテーター H-Series 1152 × 524 × 1765mm TDD-H1200WSC	581,000	608,000	1165	1165									
4-746-01	デジタルドライデンシテーター S-Series 574 × 524 × 1067mm TDD-S600CP	176,000	188,000	1164	1164									
4-746-02	デジタルドライデンシテーター S-Series 574 × 524 × 1067mm TDD-S600CS	194,000	207,000	1164	1164									
4-746-03	デジタルドライデンシテーター S-Series 574 × 524 × 1132mm TDD-S600CKP	184,000	202,000	1164	1164									
4-746-04	デジタルドライデンシテーター S-Series 574 × 524 × 1132mm TDD-S600CKS	201,000	219,000	1164	1164									
4-746-05	デジタルドライデンシテーター S-Series 1152 × 524 × 1765mm TDD-S1200WP	416,000	457,000	1164	1164									
4-746-06	デジタルドライデンシテーター S-Series 1152 × 524 × 1765mm TDD-S1200WS	449,000	491,000	1164	1164									
4-746-11	デジタルドライデンシテーター S-Series 574 × 524 × 1067mm TDD-S600CPC	186,000	200,000	1164	1164									
4-746-12	デジタルドライデンシテーター S-Series 574 × 524 × 1067mm TDD-S600CCS	202,000	217,000	1164	1164									
4-746-13	デジタルドライデンシテーター S-Series 574 × 524 × 1132mm TDD-S600CKPC	193,000	208,000	1164	1164									
4-746-14	デジタルドライデンシテーター S-Series 574 × 524 × 1132mm TDD-S600CKSC	210,000	226,000	1164	1164									
4-746-15	デジタルドライデンシテーター S-Series 1152 × 524 × 1765mm TDD-S1200WPC	423,000	461,000	1164	1164									
4-746-16	デジタルドライデンシテーター S-Series 1152 × 524 × 1765mm TDD-S1200WSC	457,000	496,000	1164	1164									
4-795-02	モーターコントロールユニット(デジタル) 角度制御タイプ PG-DE	103,000	125,000	391	391									
4-795-03	モーターコントロールユニット(デジタル) 正/逆転制御タイプ PG-FR	103,000	128,000	391	391									
4-803-01	粉体計量供給機(スクュータイプ) PSF-100SA	225,000	279,000	363	363									
4-803-02	粉体計量供給機(スクュータイプ) PSF-200SA	285,000	342,000	363	363									
5-060-01	トスロン密閉タンク 4L 白 SN-4白	2,190	2,320	1877	1877	53								
5-060-02	トスロン密閉タンク 4L 青 SN-4青	2,190	2,320	1877	1877	53								
5-060-03	トスロン密閉タンク 12L 白 SN-13白	3,880	4,090	1877	1877	53								
5-060-04	トスロン密閉タンク 12L 青 SN-13青	3,880	4,090	1877	1877	53								
5-060-05	トスロン密閉タンク 20L 白 SN-20白	4,360	4,580	1877	1877	53								
5-060-06	トスロン密閉タンク 20L 青 SN-20青	4,360	4,580	1877	1877	53								
5-060-07	トスロン密閉タンク用オープナー	2,820	2,980	1877	1877	53								
5-060-08	トスロンスケア 10L(角型)	3,670	3,870	1877	1877	53								
5-060-09	トスロン密閉タンク 3.4L 白 SN-3白	2,410	2,520	1877	1877	53								
5-1103-01	ユニットスタンドAセット	55,700	58,500	2178	2178									
5-3468-01	ジルユニア 乳鉢セット 乳鉢付き ZEX-60	73,000	84,000	344	344									
5-3468-02	ジルユニア 乳鉢セット 乳鉢付き ZEX-80	107,000	118,000	344	344									
5-3468-03	ジルユニア 乳鉢セット 乳鉢付き ZEX-100	150,000	165,000	344	344									
5-3468-04	ジルユニア 乳鉢セット 乳鉢付き ZEX-120	175,000	199,000	344	344									
5-3468-05	ジルユニア 乳鉢セット 乳鉢付き ZEX-150	240,000	264,000	344	344									
5-5350-01	直口罐詰ガラスチューブ φ10 × 75mm 1ケース(250本 × 4箱入) 14-961-25	9,800	10,300	2116	2116	853								
5-5350-02	直口罐詰ガラスチューブ φ12 × 75mm 1ケース(250本 × 4箱入) 14-961-26	11,000	11,600	2116	2116	853								
5-5350-03	直口罐詰ガラスチューブ φ13 × 100mm 1ケース(250本 × 4箱入) 14-961-27	14,200	14,900	2116	2116	853								
5-5350-04	直口罐詰ガラスチューブ φ16 × 100mm 1ケース(250本 × 4箱入) 14-961-29	21,200	22,300	2116	2116	853								
5-5350-05	直口罐詰ガラスチューブ φ16 × 125mm 1ケース(250本 × 4箱入) 14-961-30	23,900	25,100	2116	2116	853								
5-5350-06	直口罐詰ガラスチューブ φ16 × 150mm 1ケース(250本 × 4箱入) 14-961-31	25,000	26,300	2116	2116	853								
5-5350-07	直口罐詰ガラスチューブ φ18 × 150mm 1ケース(125本 × 4箱入) 14-961-32	18,300	19,200	2116	2116	853								
5-5350-08	直口罐詰ガラスチューブ φ20 × 150mm 1ケース(125本 × 4箱入) 14-961-33	27,300	28,600	2116	2116	853								
5-5350-09	直口罐詰ガラスチューブ φ25 × 150mm 1ケース(125本 × 4箱入) 14-961-34	54,000	57,000	2116	2116	853								
5-5351-03	バスツールピペット 総容量 146mm 250本/箱 × 4箱 13-678-8A	14,500	15,200	2108	2108	882								
5-5351-04	バスツールピペット 総容量 229mm 250本/箱 × 4箱 13-678-8B	16,500	17,300	2108	2108	882								
5-5353-01	罐詰ガラス製デシメトピペット(線付付・減菌済) 0.5mL 目盛0.01mL 1箱(125本 × 4箱入) 13-678-27A	37,500	40,700	2103	2103									
5-5353-02	罐詰ガラス製デシメトピペット(線付付・減菌済) 1mL 目盛0.01mL 1箱(200本 × 5箱入) 13-678-27B	60,000	64,800	2103	2103									
5-5353-03	罐詰ガラス製デシメトピペット(線付付・減菌済) 1mL 目盛0.01mL 1箱(200本 × 5箱入) 13-678-27C	58,500	63,300	2103	2103									
5-5353-04	罐詰ガラス製デシメトピペット(線付付・減菌済) 2mL 目盛0.01mL 1箱(100本 × 2箱入) 13-678-27D	27,800	38,500	2103	2103									
5-5353-05	罐詰ガラス製デシメトピペット(線付付・減菌済) 5mL 目盛0.1mL 1箱(100本 × 2箱入) 13-678-27E	35,800	49,100	2103	2103									
5-5353-06	罐詰ガラス製デシメトピペット(線付付・減菌済) 10mL 目盛0.1mL 1箱(100本 × 2箱入) 13-678-27F	51,500	55,600	2103	2103									
5-5353-07	罐詰ガラス製デシメトピペット(線付付・減菌済) 1mL 目盛0.01mL 1箱(200本 × 2箱入) 13-678-36A	42,800	45,500	2103	2103									
5-5353-08	罐詰ガラス製デシメトピペット(線付付・減菌済) 5mL 目盛0.1mL 1箱(100本 × 2箱入) 13-678-36B	25,500	27,500	2103	2103									
5-5353-09	罐詰ガラス製デシメトピペット(線付付・減菌済) 10mL 目盛0.2mL 1箱(100本 × 2箱入) 13-678-36C	42,500	45,900	2103	2103									
5-5353-10	罐詰ガラス製デシメトピペット(線付付・減菌済) 25mL 目盛0.2mL 1箱(100本 × 2箱入) 13-678-36D	69,000	74,500	2103	2103									
5-5353-11	罐詰ガラス製デシメトピペット(線付付・減菌済) 50mL 目盛0.5mL 1箱(25本 × 2箱入) 13-678-36E	74,000	80,100	2103	2103									
5-5356-01	ポリエチレンひしゃく 14-242-20	2,340	2,700	2225	2225									
5-5356-02	ポリエチレンひしゃく 14-242-25	2,690	3,100	2225	2225									
5-5356-03	ポリエチレンひしゃく 14-242-30	2,920	3,400	2225	2225									
5-5356-05	ポリエチレンひしゃく 14-242-40	3,780	4,300	2225	2225									
5-5356-06	ポリエチレンひしゃく 14-242-45	7,970	9,100	2225	2225									
61-0001-23	デュボン(TM)タイプベック(R)製 ジャンパー M 2110A-M	1,150	1,270	2951	2951									
61-0001-24	デュボン(TM)タイプベック(R)製 ジャンパー L 2110A-L	1,150	1,270	2951	2951									
61-0001-25	デュボン(TM)タイプベック(R)製 ジャンパー LL 2110A-LL	1,150	1,270	2951	2951									
61-0001-26	デュボン(TM)タイプベック(R)製 ジャンパー 3L 2110A-3L	1,150	1,270	2951	2951									
61-0001-50	デュボン(TM)タイプベック(R)製 シューズカバー(短・特大)(10双入) 6863	3,450	3,850	2982	2982									
61-0001-52	ポリエチレン製シューズカバー(すべり止め・短)(10双入) 6864	4,100	4,650	2982	2982									
61-0001-53	ポリエチレン製シューズカバー(すべり止め・短・特大)(10双入) 6865	5,050	5,750	2982	2982									
61-0168-93	Eppendorf Safe-Lock Tubes, 0.5mL, PCR clean, 500本 0030 123.301	9,100	7,400	-	-									
61-0528-83	カラールBP&コビー用耐水紙ラベル A4 100枚入 ノーカット LBP-WP1900N	13,200	13,000	2450	2450									
61-0528-85	カラールBP&コビー用耐水紙ラベル A4 20枚入 ノーカット LBP-WP6900N	2,610	2,620	2450	2450									

品番	商品名	旧価格	新価格	研究用総合 機種2023 頁	サンクス2023 頁	ナビス2024 頁	サニーク 2024 頁	設備2024 頁	アズビエ 2023 頁	アズツール 2021 頁	ナビ動2023 頁	産総研対策 用品パンフ 頁	ウェルビー イングラン ド 頁	サイエンス カタログ 頁
61-6021-18	児童用安全めがね 8595	410	440											581
61-6021-28	手作り天体望遠鏡 8613	1,520	1,570											565
61-7667-89	ダイヤフラム式ドライ真空ポンプ N816.3KT.18	155,000	163,000	445	445									
61-7668-32	送液ポンプ NF300KT.18S	144,000	159,000	406	406									
61-7668-34	送液ポンプ NF300FT.18S	432,000	476,000	406	406									
61-7668-38	送液ポンプ NF300KT.18RC	174,000	192,000	406	406									
61-7668-40	送液ポンプ NF300FT.18RC	462,000	509,000	406	406									
61-7668-44	送液ポンプ NF100FT.18S	337,000	371,000	406	406									
61-7668-48	送液ポンプ NF100KT.18RC	144,000	159,000	406	406									
61-7668-49	送液ポンプ NF100FT.18RC	367,000	404,000	406	406									
61-8015-35	新生児用ディスポーサルカフ SOFTカフ 3.3~5.6cm 10枚入 5082-101-1	10,200	11,300			670								
61-8015-36	新生児用ディスポーサルカフ SOFTカフ 4.2~7.1cm 10枚入 5082-102-1	10,200	11,300			670								
61-8015-37	新生児用ディスポーサルカフ SOFTカフ 5.4~9.1cm 10枚入 5082-103-1	10,200	11,300			670								
61-8015-38	新生児用ディスポーサルカフ SOFTカフ 6.9~11.7cm 10枚入 5082-104-1	10,200	11,300			670								
61-8015-39	新生児用ディスポーサルカフ SOFTカフ 8.9~15.0cm 10枚入 5082-105-1	10,200	11,300			670								
61-9630-06	フェアリーチェア50 BR-FC50	63,000	70,000				1023							
61-9630-07	フェアリーチェア35 BR-ST35	52,000	59,000				1023							
61-9630-08	フェアリーチェア90 BR-FC90	105,000	120,000				1023							
61-9869-04	患者衣(上衣・男女兼用) ブルー×ピンク S 285-98 S	2,600	2,800				425							
61-9869-05	患者衣(上衣・男女兼用) ブルー×オレンジ M 285-98 M	2,600	2,800				425							
61-9869-06	患者衣(上衣・男女兼用) ブルー×ブラウン L 285-98 L	2,600	2,800				425							
61-9869-07	患者衣(上衣・男女兼用) ブルー×グリーン LL 285-98 LL	2,600	2,800				425							
61-9869-08	患者衣(上衣・男女兼用) ブルー×ネイビー 3L 285-98 3L	2,600	2,800				425							
61-9869-38	患者衣(スラックス・男女兼用) ブルー×ピンク S 286-98 S	2,500	2,700				425							
61-9869-39	患者衣(スラックス・男女兼用) ブルー×オレンジ M 286-98 M	2,500	2,700				425							
61-9869-40	患者衣(スラックス・男女兼用) ブルー×ブラウン L 286-98 L	2,500	2,700				425							
61-9869-41	患者衣(スラックス・男女兼用) ブルー×グリーン LL 286-98 LL	2,500	2,700				425							
61-9869-42	患者衣(スラックス・男女兼用) ブルー×ネイビー 3L 286-98 3L	2,500	2,700				425							
61-9869-82	患者衣ガウン(男女兼用) ブルー×ピンク S 289-98 S	3,600	3,800				425							
61-9869-83	患者衣ガウン(男女兼用) ブルー×オレンジ M 289-98 M	3,600	3,800				425							
61-9869-84	患者衣ガウン(男女兼用) ブルー×ブラウン L 289-98 L	3,600	3,800				425							
61-9869-85	患者衣ガウン(男女兼用) ブルー×グリーン LL 289-98 LL	3,600	3,800				425							
61-9869-86	患者衣ガウン(男女兼用) ブルー×ネイビー 3L 289-98 3L	3,600	3,800				425							
62-1362-36	ポータブル天びん スカウトシリーズ(フルカラータッチスクリーン搭載モデル)120g/0.001g STX123JP	94,000	95,900	499	499									
62-1362-37	ポータブル天びん スカウトシリーズ(フルカラータッチスクリーン搭載モデル)220g/0.001g STX223JP	98,200	100,200	476	476									
62-1362-38	ポータブル天びん スカウトシリーズ(フルカラータッチスクリーン搭載モデル)220g/0.01g STX222JP	63,700	65,000	499	499									
62-1362-39	ポータブル天びん スカウトシリーズ(フルカラータッチスクリーン搭載モデル)420g/0.01g STX422JP	80,300	82,000	499	499									
62-1362-40	ポータブル天びん スカウトシリーズ(フルカラータッチスクリーン搭載モデル)620g/0.01g STX622JP	82,800	84,500	499	499									
62-1362-43	ポータブル天びん スカウトシリーズ(フルカラータッチスクリーン搭載モデル)420g/0.1g STX421JP	60,900	62,200	477	477									
62-1362-44	ポータブル天びん スカウトシリーズ(フルカラータッチスクリーン搭載モデル)620g/0.1g STX621JP	62,400	63,700	477	477									
62-1362-45	ポータブル天びん スカウトシリーズ(フルカラータッチスクリーン搭載モデル)2200g/0.1g STX2201JP	70,600	72,100	499	499									
62-1362-46	ポータブル天びん スカウトシリーズ(フルカラータッチスクリーン搭載モデル)6200g/0.1g STX6201JP	78,700	80,300	499	499									
62-1362-67	ハロゲン水分計(タッチスクリーンモデル) MB120	279,300	284,900	851	851									
62-1362-68	ハロゲン水分計(タッチスクリーンモデル) MB90	234,100	238,800	851	851									
62-1609-30	ヘマドシール キヤピラリーチューブシーラント 箱(10本入) 02-678	7,500	8,100	1487	1487									
62-1610-43	セフティーマット 510×610mm 1/2ツグ(50シート入) 14-206-62	11,000	13,400	3007	3007									843
62-1610-45	セフティーマット 510mm×30m 14-206-64	12,500	15,200	3007	3007									
62-1610-46	セフティーマット 510mm×76m 14-206-65	27,000	32,900	3007	3007									
6-219-01	TPXビーカー 100mL(手なし)	200	220	2065	2065									
6-219-02	TPXビーカー 200mL(手なし)	280	310	2065	2065									
6-219-03	TPXビーカー 300mL(手なし)	330	370	2065	2065									
6-219-04	TPXビーカー 500mL(手なし)	500	550	2065	2065									
6-219-05	TPXビーカー 1L(手なし)	850	940	2065	2065									
6-220-01	TPX手付きビーカー 100mL	300	330	2065	2065									
6-220-02	TPX手付きビーカー 200mL	330	370	2065	2065									
6-220-03	TPX手付きビーカー 300mL	440	490	2065	2065									
6-220-04	TPX手付きビーカー 500mL	550	610	2065	2065									
6-220-05	TPX手付きビーカー 1L	1,100	1,210	2065	2065									
6-220-06	TPX手付きビーカー 2L	1,320	1,460	2065	2065									
6-220-07	TPX手付きビーカー 3L	2,200	2,400	2065	2065									
6-220-08	TPX手付きビーカー 5L	3,300	3,600	2065	2065									
62-2252-49	マルチシート穴あけマスター 60mm #1720	1,250	1,320	1576	1576									
62-2252-50	マルチシート穴あけマスター 80mm #1721	1,330	1,440	1576	1576									
62-2252-51	マルチシート穴あけマスター 100mm #1722	1,500	1,620	1576	1576									
62-2252-53	アンカー抜き 農芸用 アルミ柄 #1646	3,360	3,580	1574	1574									
62-2642-85	高配向性黒鉛(HOPG-ZYA)基板 両面磨削 10×10×1.5mm 1枚 HOPG-1.5A-□10-1	114,000	126,000	2350	2350									
62-2642-86	高配向性黒鉛(HOPG-ZYA)基板 両面磨削 10×10×1.0mm 1枚 HOPG-1A-□10-1	87,000	101,000	2350	2350									
62-2642-87	高配向性黒鉛(HOPG-ZYB)基板 両面磨削 10×10×1.5mm 1枚 HOPG-1.5B-□10-1	52,000	59,800	2350	2350									
62-2642-88	高配向性黒鉛(HOPG-ZYB)基板 両面磨削 10×10×1.0mm 1枚 HOPG-1B-□10-1	41,500	48,300	2350	2350									
62-2642-90	高配向性黒鉛(HOPG-ZYH)基板 両面磨削 10×10×2.0mm 5枚入 HOPG-2H-□10-5	150,000	165,000	2350	2350									
62-2642-91	高配向性黒鉛(HOPG-ZYH)基板 両面磨削 10×10×1.5mm 1枚 HOPG-1.5H-□10-1	33,800	31,900	2350	2350									
62-2642-94	高配向性黒鉛(HOPG-ZYH)基板 両面磨削 10×10×1.0mm 5枚入 HOPG-1H-□10-5	124,500	130,000	2350	2350									
62-2977-97	WA電顕鏡 予備電球LED 2.5V 06000-LED	27,000	29,700				968							
6-236-01	TPX(R)メスシリンダー ポリメチルペンテン 10mL	550	610	2088	2088									
6-236-02	TPX(R)メスシリンダー ポリメチルペンテン 20mL	660	730	2088	2088									
6-236-03	TPX(R)メスシリンダー ポリメチルペンテン 50mL	880	970	2088	2088									
6-236-04	TPX(R)メスシリンダー ポリメチルペンテン 100mL	990	1,090	2088	2088									
6-236-05	TPX(R)メスシリンダー ポリメチルペンテン 200mL	1,320	1,460	2088	2088									
6-236-06	TPX(R)メスシリンダー ポリメチルペンテン 300mL	1,540	1,700	2088	2088									
6-236-07	TPX(R)メスシリンダー ポリメチルペンテン 500mL	2,750	3,000	2088	2088									
6-236-08	TPX(R)メスシリンダー ポリメチルペンテン 1L	4,400	4,800	2088	2088									
6-236-09	TPX(R)メスシリンダー ポリメチルペンテン 2L	5,500	6,000	2088	2088									
62-3807-84	WA電顕鏡 プレート LED電顕鏡セット ミラール 68696-LED	111,900	134,300				967							
62-3807-85	WA電顕鏡 プレート LED電顕鏡セット マットレス型 68696-LED	104,500	125,400				967							
62-3807-86	WA電顕鏡 プレート LED電顕鏡セット イングリッシュマッキントッシュ型 68697-LED	123,500	148,200				967							
62-4114-68	フラットアンカー(φ4mm×20cm 10P) #7702	410	420	1574	1574									
62-4533-29	ミニパワーリレー(MY2形) 動作表示灯内蔵形 MY2ZN DC24	1,890	2,250	3405	3405									
62-4533-30	ミニパワーリレー(MY2形) ダイオード・動作表示灯内蔵形 MY2ZN-D2 DC24	2,130	2,600	3405	3405									
62-4611-23	スマートセンサ レーザ変位センサ CMOSタイプ ZX2シリーズ ZX2-LD100L 0.5M	73,800	81,300	3416	3416									
62-4611-24	スマートセンサ レーザ変位センサ CMOSタイプ ZX2シリーズ ZX2-LD100 0.5M	73,800	81,300	3416	3416									
62-4611-25	スマートセンサ レーザ変位センサ CMOSタイプ ZX2シリーズ ZX2-LD50L 0.5M	73,800	81,300	3416	3416									
62-4611-26	スマートセンサ レーザ変位センサ CMOSタイプ ZX2シリーズ ZX2-LD50 0.5M	73,800	81,300	3416	3416									
62-4611-29	スマートセンサ レーザ変位センサ CMOSタイプ ZX2シリーズ ZX2-LDA41 2M	41,300	45,500	3416	3416									
62-4611-30	スマートセンサ レーザ変位センサ CMOSタイプ ZX2シリーズ ZX2-LDA11 2M	41,300	45,500	3416	3416									
62-4765-29	フロートなしスイッチ(ベースタイプ) 61F-G□ 61F-G□ AC100/200	34,000	37,500	3396	3396									
62-4765-43	フロートなしスイッチ(ベースタイプ) 61F-G□ 61F-G□ AC100/200	21,000	23,000	3396	3396									
62-4765-58	フロートなしスイッチ(ベースタイプ) 61F-G□ 61F-G□ AC100/200	15,000	16,500	3396	3396									
62-4765-72	フロートなしスイッチ(ベースタイプ) 61F-G□ 61F-G□ AC100/200	15,000	16,500	3396	3396									
62-4765-85	フロートなしスイッチ用リレーユニット 61F-11	5,400	5,950	3396	3396									
62-4768-08	フロートなしスイッチ(ベースタイプ) 61F-G□ 61F-G□ AC100/200	11,100	12,200	3396	3396	</								

品番	商品名	旧価格	新価格	研究用総合 機種2023 頁	サンクス2023 頁	ナビス2024 頁	サニーブルー 2024 頁	数値2024 頁	アズビエア 2023 頁	アズツール 2021 頁	ナビ動2023 頁	産産産産 用種パンフ 頁	ウェルビー イングラン ツ 頁	サイエンス カタログ 頁
62-6180-20	13mm GD/メスリソジフィルター(NYL 0.45 μm)1パック(150個入) 6870-1304	58,000	59,200	1666	1666									
62-6180-31	13mm GD/メスリソジフィルター(PTFE 0.2 μm)1パック(150個入) 6874-1302	58,000	59,200	1666	1666									
62-6180-32	13mm GD/メスリソジフィルター(PTFE 0.45 μm)1パック(150個入) 6874-1304	58,000	59,200	1666	1666									
62-6180-37	13mm GD/メスリソジフィルター(PES 0.2 μm)1パック(150個入) 6876-1302	58,000	59,200	1666	1666									
62-6180-55	13mm GD/メスリソジフィルター(GF/B 1.0 μm)1パック(150個入) 6884-1310	58,000	59,200	1667	1667									
62-6180-56	25mm GD/メスリソジフィルター(GF/B 1.0 μm)1パック(150個入) 6884-2510	65,200	66,500	1667	1667									
62-6180-59	25mm GD/メスリソジフィルター(RC 0.2 μm)1パック(150個入) 6887-2502	65,200	66,500	1667	1667									
62-6180-61	25mm GD/メスリソジフィルター(GF/D 2.7 μm)1パック(150個入) 6888-2527	65,200	66,500	1667	1667									
62-6180-66	13mm GD/メスリソジフィルター(GMF 0.45 μm)1パック(150個入) 6884-1304	58,000	59,200	1667	1667									
62-6180-67	25mm GD/メスリソジフィルター(GMF 0.45 μm)1パック(150個入) 6884-2504	65,200	66,500	1667	1667									
62-7041-51	インセクトボイジンリムーバー HSD1100000	1,200	1,300	3095	3095									
62-9986-86	丸型濾過管 100mL 109012	3,850	8,200	2129	2129									
62-9986-87	丸型濾過管 250mL 109013	9,800	10,800	2129	2129									
63-1202-77	セミクロ天びん ハイオニアシリーズ 82g PX85JP	322,300	328,800	476	476									
63-1202-93	分析天びん ハイオニアシリーズ 82g PX84JP	183,400	187,100	476	476									
63-1202-96	分析天びん ハイオニアシリーズ 220g PX223JP	105,400	107,600	476	476									
63-1203-01	上皿天びん ハイオニアシリーズ 3200g PX3202JP	118,200	120,600	477	477									
63-1204-16	メジャーケース 1箱(3個入) 26101	2,000	6,000			1016								
6-319-01	TPX(R)ハイスピードロータ φ60mm	200	220	2156	2156									494
6-319-02	TPX(R)ハイスピードロータ φ75mm	240	270	2156	2156									494
6-319-03	TPX(R)ハイスピードロータ φ90mm	360	400	2156	2156									494
6-319-04	TPX(R)ハイスピードロータ φ120mm	600	660	2156	2156									494
6-319-05	TPX(R)ハイスピードロータ φ150mm	1,200	1,320	2156	2156									494
6-319-06	TPX(R)ハイスピードロータ φ180mm	1,800	1,980	2156	2156									494
6-319-07	TPX(R)ハイスピードロータ φ210mm	2,400	2,600	2156	2156									494
6-319-08	TPX(R)ハイスピードロータ φ240mm	3,000	3,300	2156	2156									494
6-319-09	TPX(R)ハイスピードロータ φ300mm	3,800	3,900	2156	2156									494
63-3099-90	プレートボード 16541102BE	2,100	3,220	2568	2568									
63-3099-91	プレートボード 165411060E	3,620	5,640	2568	2568									
63-3102-63	プレートボード(EIC104J) 0165-41-4-1040	2,960	4,990	2568	2568									
63-3136-20	ACアダプター 3.3V 2A ATS012T-W033U	1,160	1,870	3417	3417									
63-3136-21	ACアダプター 5V 2.5A ATS012T-W051U	1,160	1,870	3417	3417									
63-3136-22	ACアダプター 5V 3A ATS018T-W050U	1,300	2,000	3417	3417									
63-3136-23	ACアダプター 5V 4A ATS024T-W050U	1,430	2,150	3417	3417									
63-3136-24	ACアダプター 9V 2.5A ATS024T-W090U	1,430	2,150	3417	3417									
63-3136-25	ACアダプター 12V 1A ATS012T-W120U	1,160	1,870	3417	3417									
63-3136-26	ACアダプター 12V 1.6A ATS018T-W120U	1,300	2,000	3417	3417									
63-3136-27	ACアダプター 12V 2A ATS024T-W120U	1,430	2,150	3417	3417									
63-3136-29	ACアダプター 15V 1.6A ATS024T-W150U	1,430	2,150	3417	3417									
63-3136-30	ACアダプター 24V 1A ATS024T-W240U	1,430	2,150	3417	3417									
63-3154-36	MESH Button(ボタン)タグ MESH-100BU	7,900	8,700	2568	2568									
63-3154-38	MESH Move(動き)タグ MESH-100AC	7,900	8,700	2568	2568									
63-3154-41	MESH Brightness(明るさ)タグ MESH-100PA	9,300	10,200	2568	2568									
63-3154-42	MESH Motion(人感)タグ MESH-100MD	9,300	10,200	2568	2568									
63-4154-92	フッ素樹脂(PTFE)1/4L型攪拌棒 φ8×450L NR6706-001	29,000	37,000	225	225									
63-4154-93	フッ素樹脂(PTFE)1/4L型攪拌棒 φ8×500L NR6706-002	29,000	38,000	225	225									
63-4154-94	フッ素樹脂(PTFE)1/4L型攪拌棒 φ8×600L NR6706-003	30,000	39,000	225	225									
63-4154-95	フッ素樹脂(PTFE)1/4L型攪拌棒 φ8×700L NR6706-004	33,000	40,000	225	225									
63-4154-96	フッ素樹脂(PTFE)1/4L型攪拌棒 φ8×800L NR6706-005	36,000	41,000	225	225									
63-4217-69	オイルドレインキット ODK-UL(M10)	25,000	29,000	460	460									
63-4217-70	オイルドレインキット ODK-UL(M8)	25,000	29,000	460	460									
63-5729-31	コンパクト天びん コンパSCRシリーズ 2200g 1g CR2200JP	13,300	13,600	505	505									
63-5729-32	コンパクト天びん コンパSCRシリーズ 5200g 1g CR5200JP	16,800	17,000	505	505									
63-5729-38	コンパクト電子天びん ナビゲーター-NVシリーズ 620g 0.01g NV622JP	60,400	61,700	502	502									
63-5729-39	コンパクト電子天びん ナビゲーター-NVシリーズ 220g 0.1g NV221JP	37,700	38,500	477	477									
63-5729-40	コンパクト電子天びん ナビゲーター-NVシリーズ 1200g 0.1g NV1201JP	39,000	39,800	477	477									
63-5729-43	コンパクト電子天びん ナビゲーター-NVTシリーズ 6200g 0.1g NV6201JP	55,100	56,300	502	502									
6-391-01	組立スタンド 90型	51,600	53,900	2178	2178									
6-391-02	組立スタンド 120型	60,200	72,700	2178	2178									
63-9286-04	テフロンルーロックシリソジ 0.25mL MS-GLL025	13,500	14,500	-	-									
63-9286-05	テフロンルーロックシリソジ 0.5mL MS-GLL050	13,500	14,500	-	-									
63-9286-06	テフロンルーロックシリソジ 1mL MS-GLL100	14,300	15,300	-	-									
63-9286-07	テフロンルーロックシリソジ 2.5mL MS-GLL250	14,300	15,300	-	-									
63-9286-08	テフロンルーロックシリソジ 25mL MS-GLL2500	63,000	73,000	-	-									
63-9286-09	テフロンルーロックシリソジ 5mL MS-GLL500	15,800	16,800	-	-									
63-9286-10	テフロンルーロックシリソジ 10mL MS-GLLX00	18,600	19,600	-	-									
63-9286-49	テフロンルーロックシリソジ 0.05mL MS-GLL005	15,500	16,500	-	-									
63-9286-50	テフロンルーロックシリソジ 0.1mL MS-GLL010	15,500	16,500	-	-									
63-9286-51	テフロンルーロックシリソジ 50mL MS-GLL5000	87,000	110,000	-	-									
63-9286-52	テフロンルーロックシリソジ 100mL MS-GLLX000	132,000	189,000	-	-									
63-9286-53	UNFネジシリソジ 25mL MS-UNF2500	56,500	69,000	-	-									
63-9286-54	UNFネジシリソジ 50mL MS-UNF5000	81,000	99,000	-	-									
63-9286-55	UNFネジシリソジ 100mL MS-UNFX000	123,000	150,000	-	-									
6-4047-21	デジタル照度計 LX-2500	32,700	28,000	761	761	131								521
6-4047-22	デジタル照度計 LX-3000	36,300	33,000	761	761	131								521
64-0697-59	フォースゲージ 出力付 2N FGP-0.2	91,000	117,000	-	-									
64-0697-61	フォースゲージ 出力付 10N FGP-1	91,000	117,000	-	-									
64-0697-64	フォースゲージ 出力付 20N FGP-2	91,000	117,000	-	-									
64-0697-68	フォースゲージ 出力付 50N FGP-5	84,000	99,600	-	-									
6-413-11	チェーンクランプ 02-214-149	22,800	26,500	2192	2192									
64-3697-87	ブラディスク13(親水性PTFE 0.2 μm)100個入 6772-1302	28,100	28,700	1666	1666									
64-3697-88	ブラディスク13(親水性PTFE 0.45 μm)100個入 6772-1304	28,100	28,700	1666	1666									
64-3697-89	ブラディスク25(親水性PTFE 0.2 μm)50個入 6772-2502	14,190	14,470	1666	1666									
64-3697-90	ブラディスク25(親水性PTFE 0.45 μm)50個入 6772-2504	14,190	14,470	1666	1666									
64-3703-61	ブラグ SUS 1個入 1/16 ZP1	4,500	4,800	-	-									
64-3703-62	ブラグ SUS 1個入 1/16 ロング LZP1	3,800	4,000	-	-									
64-3703-63	ブラグ SUS 1個入 1/8 ZP2	4,500	4,800	-	-									
64-3703-64	ブラグ SUS 1個入 1/8 ロング LZP2	3,800	4,000	-	-									
64-3967-90	ダスタッパNR BR-NR-DST	80,000	92,000			1022								
64-3967-91	ダスタッパNW BR-NW-DST	84,000	92,000			1022								
6-451-01	ジャンボトング 15-207	12,100	14,400	2228	2228									
6-451-02	トング ビーカー用 02-620	10,000	12,400	2228	2228									
64-5857-61	アルミ製ノートパソコンスタンド(スタンディング対応) CR-39	18,290	24,000											
64-6360-89	防塵型・耐薬品性真空ポンプ 289×240×177mm N840G	329,000	346,000	445	445									
64-8206-14	モンシロチョウの卵 10個 (販売期間:4月15日～7月15日)	2,060	2,100	1527	1527									
64-8206-15	モンシロチョウの卵 20個 (販売期間:4月15日～7月15日)	3,090	3,390	1527	1527									
64-8206-16	モンシロチョウの卵 30個 (販売期間:4月15日～7月15日)	3,860	4,100	1527	1527									
64-8206-17	モンシロチョウの卵 40個 (販売期間:4月15日～7月15日)	5,150	5,270	1527	1527									
64-8206-18	モンシロチョウの卵 50個 (販売期間:4月15日～7月15日)	6,180	6,440	1527	1527									
64-8206-19	モンシロチョウの卵 100個 (販売期間:4月15日～7月15日)	11,580	12,900	1527	1527									
64-8206-20	モンシロチョウの幼虫 10匹 (販売期間:4月15日～7月15日)	3,090	3,160	1527	1527									

品番	商品名	旧価格	新価格	研究用総合 機種2023 頁	サンクス 2023 頁	ナビス2024 頁	サニーフーズ 2024 頁	設備2024 頁	アズビエア 2023 頁	アズツール 2021 頁	ナビ助2023 頁	産産産産産 用品パンフ 頁	ウェルビー イングラン ツ 頁	サイエンス カタログ 頁
67-4791-23	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13326	173.800	177.100	-	-	-	-	-	-	-	-	-	-	-
67-4791-24	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13327	182.800	186.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-25	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13335	64.500	65.800	-	-	-	-	-	-	-	-	-	-	-
67-4791-26	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13336	68.800	70.100	-	-	-	-	-	-	-	-	-	-	-
67-4791-27	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13337	73.100	74.500	-	-	-	-	-	-	-	-	-	-	-
67-4791-28	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13338	103.600	105.500	-	-	-	-	-	-	-	-	-	-	-
67-4791-29	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13339	107.800	109.700	-	-	-	-	-	-	-	-	-	-	-
67-4791-30	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13340	119.900	122.100	-	-	-	-	-	-	-	-	-	-	-
67-4791-31	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13341	173.800	177.100	-	-	-	-	-	-	-	-	-	-	-
67-4791-32	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13342	182.800	186.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-33	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13350	64.500	65.800	-	-	-	-	-	-	-	-	-	-	-
67-4791-34	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13352	73.100	74.500	-	-	-	-	-	-	-	-	-	-	-
67-4791-35	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13353	103.600	105.500	-	-	-	-	-	-	-	-	-	-	-
67-4791-36	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13354	107.800	109.700	-	-	-	-	-	-	-	-	-	-	-
67-4791-37	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13355	119.900	122.100	-	-	-	-	-	-	-	-	-	-	-
67-4791-38	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13356	173.800	177.100	-	-	-	-	-	-	-	-	-	-	-
67-4791-39	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13357	182.800	186.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-40	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13367	73.100	74.500	-	-	-	-	-	-	-	-	-	-	-
67-4791-41	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13370	119.900	122.100	-	-	-	-	-	-	-	-	-	-	-
67-4791-42	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13373	195.800	199.600	-	-	-	-	-	-	-	-	-	-	-
67-4791-43	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13396	107.800	109.700	-	-	-	-	-	-	-	-	-	-	-
67-4791-44	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13397	63.600	64.900	-	-	-	-	-	-	-	-	-	-	-
67-4791-45	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13398	94.300	96.100	-	-	-	-	-	-	-	-	-	-	-
67-4791-46	GC、GC/MS用キャピラリーカラム Rxi(R)-1ms 13399	152.800	155.700	-	-	-	-	-	-	-	-	-	-	-
67-4791-47	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13401	79.800	81.300	-	-	-	-	-	-	-	-	-	-	-
67-4791-48	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13402	84.900	86.600	-	-	-	-	-	-	-	-	-	-	-
67-4791-49	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13409	84.900	86.600	-	-	-	-	-	-	-	-	-	-	-
67-4791-50	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13411	84.900	86.600	-	-	-	-	-	-	-	-	-	-	-
67-4791-51	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13420	63.600	64.900	-	-	-	-	-	-	-	-	-	-	-
67-4791-52	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13421	67.300	68.600	-	-	-	-	-	-	-	-	-	-	-
67-4791-53	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13422	71.800	73.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-54	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13423	99.000	105.800	-	-	-	-	-	-	-	-	-	-	-
67-4791-55	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13424	106.100	111.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-56	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13425	117.500	123.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-57	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13426	170.400	178.600	-	-	-	-	-	-	-	-	-	-	-
67-4791-58	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13427	179.500	188.100	-	-	-	-	-	-	-	-	-	-	-
67-4791-59	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13435	63.600	64.900	-	-	-	-	-	-	-	-	-	-	-
67-4791-60	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13436	67.300	68.600	-	-	-	-	-	-	-	-	-	-	-
67-4791-61	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13437	71.800	73.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-62	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13438	101.000	105.800	-	-	-	-	-	-	-	-	-	-	-
67-4791-63	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13439	106.100	111.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-64	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13440	117.500	123.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-65	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13441	170.400	178.600	-	-	-	-	-	-	-	-	-	-	-
67-4791-66	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13442	179.500	188.100	-	-	-	-	-	-	-	-	-	-	-
67-4791-67	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13450	63.600	64.900	-	-	-	-	-	-	-	-	-	-	-
67-4791-68	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13451	67.300	68.600	-	-	-	-	-	-	-	-	-	-	-
67-4791-69	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13452	71.800	73.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-70	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13453	101.000	105.800	-	-	-	-	-	-	-	-	-	-	-
67-4791-71	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13454	106.100	111.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-72	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13455	117.500	123.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-73	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13456	170.400	178.600	-	-	-	-	-	-	-	-	-	-	-
67-4791-74	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13457	179.500	188.100	-	-	-	-	-	-	-	-	-	-	-
67-4791-75	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13467	71.800	73.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-76	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13470	117.500	123.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-77	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13481	101.000	105.800	-	-	-	-	-	-	-	-	-	-	-
67-4791-78	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13497	62.700	63.900	-	-	-	-	-	-	-	-	-	-	-
67-4791-79	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13498	92.300	96.700	-	-	-	-	-	-	-	-	-	-	-
67-4791-80	GC、GC/MS用キャピラリーカラム Rxi(R)-5ms 13499	149.900	157.000	-	-	-	-	-	-	-	-	-	-	-
67-4791-95	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13605	69.800	73.800	-	-	-	-	-	-	-	-	-	-	-
67-4791-96	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13608	106.900	110.900	-	-	-	-	-	-	-	-	-	-	-
67-4791-97	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13620	69.800	73.800	-	-	-	-	-	-	-	-	-	-	-
67-4791-98	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13621	73.900	78.200	-	-	-	-	-	-	-	-	-	-	-
67-4791-99	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13623	99.000	102.500	-	-	-	-	-	-	-	-	-	-	-
67-4792-01	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13624	114.600	119.100	-	-	-	-	-	-	-	-	-	-	-
67-4792-02	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13626	180.300	187.300	-	-	-	-	-	-	-	-	-	-	-
67-4792-03	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13635	69.800	73.800	-	-	-	-	-	-	-	-	-	-	-
67-4792-04	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13638	106.900	110.900	-	-	-	-	-	-	-	-	-	-	-
67-4792-05	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13639	114.600	119.100	-	-	-	-	-	-	-	-	-	-	-
67-4792-06	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13650	69.800	73.800	-	-	-	-	-	-	-	-	-	-	-
67-4792-07	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13653	106.900	110.900	-	-	-	-	-	-	-	-	-	-	-
67-4792-08	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13654	114.600	119.100	-	-	-	-	-	-	-	-	-	-	-
67-4792-09	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13670	127.400	132.300	-	-	-	-	-	-	-	-	-	-	-
67-4792-10	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 13697	180.300	187.300	-	-	-	-	-	-	-	-	-	-	-
67-4796-77	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 43601	79.800	84.400	-	-	-	-	-	-	-	-	-	-	-
67-4796-78	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 43602	92.300	95.800	-	-	-	-	-	-	-	-	-	-	-
67-4796-79	GC、GC/MS用キャピラリーカラム Rxi(R)-5Sil MS 43604	92.300	95.800	-	-	-	-	-	-	-	-	-	-	-
67-4797-97	GC、GC/MS用キャピラリーカラム MXT(R)-5 70257	194.200	211.400	-	-	-	-	-	-	-	-	-	-	-
67-4797-98	GC、GC/MS用キャピラリーカラム MXT(R)-5 70258	199.300	217.000	-	-	-	-	-	-	-	-	-	-	-
6-7997-11	真空計 アクティブデジタルコントローラ (拡張) D395-91-500	180.000	198.000	805	805	-	-	-	-	-	-	-	-	-
6-7997-12	真空計 アクティブデジタルコントローラ (標準) D395-90-000	135.000	148.000	805	805	-	-	-	-	-	-	-	-	-
67-6612-27	FAテスト II 抽出用試薬 08627	10.000	11.000	-	-	-	99	-	-	-	-	-	-	-
6-7783-01	縮小交換用ピース NW25/10 (SUS316L) C10514446	9.860	10.900	465	465	-	-	-	-	-	-	-	-	-
6-7783-02	縮小交換用ピース NW25/16 (SUS316L) C10514447	10.800	11.900	465	465	-	-	-	-	-	-	-	-	-
6-7783-03	縮小交換用ピース NW40/16 (SUS316L) C10516448	12.000	13.100	465	465	-	-	-	-	-	-	-	-	-
6-7783-04	縮小交換用ピース NW40/25 (SUS316L) C10516449	12.300	13.600	465	465	-	-	-	-	-	-	-	-	-
6-7783-05	縮小交換用ピース NW50/16 (SUS316L) C10517450	14.100	15.500	465	465	-	-	-	-	-	-	-	-	-
6-7783-06	縮小交換用ピース NW50/25 (SUS316L) C10517051	14.100	15.500	465	465	-	-	-	-	-	-	-	-	-
6-7783-07	縮小交換用ピース NW50/40 (SUS316L) C10517452	18.000	19.800	465	465	-	-	-	-	-	-	-	-	-
6-7784-01	縮小交換用Tピース NW25/16 (SUS316L) C105-14-427	23.100	25.400	465	465	-	-	-	-	-	-	-	-	-
6-7784-02	縮小交換用Tピース NW40/16 (SUS316L) C105-16-428	24.400	26.800	465	465	-	-	-	-	-	-	-	-	-
6-7784-03	縮小交換用Tピース NW40/25 (SUS316L) C105-16-429	24.400	26.800	465	465	-	-	-	-	-	-	-	-	-
6-7784-04	縮小交換用Tピース NW50/16 (SUS316L) C105-17-430	33.300	36.600	465	465	-	-	-	-	-	-	-	-	-
6-7784-05	縮小交換用Tピース NW50/25 (SUS316L) C105-17-431	33.300	36.600	465	465	-	-	-	-	-	-	-	-	-
67-8041-04	エコミー台はかり・シッピングスケール 秤量9kg 最小表示0.005kg C12P9JP	28.900	29.500	-	-	-	-	-	-	-	-	-	-	-
67-8041-05	エコミー台はかり・シッピングスケール 秤量20kg 最小表示0.01kg C12P20JP	28.												

品番	商品名	旧価格	新価格	研究用総合 機種2023 頁	サンクアス ト 2023 頁	ナビス2024 頁	サニーフー ズ2024 頁	設備2024 頁	アズビエア 2023 頁	アズツール 2021 頁	ナビ助2023 頁	産産産育養 用品/パンフ 頁	ウェルビー イングパン フ 頁	サイエンス カタログ 頁
68-0329-16	InertCap 5MS 0.32mmX60M df=0.25um 1010-18762	161,000	177,000	-	-	-	-	-	-	-	-	-	-	-
68-0329-21	InertCap AQUATIC-2 0.25mmX30M df=1.4um 1010-19146	85,000	94,800	-	-	-	-	-	-	-	-	-	-	-
68-0329-22	InertCap AQUATIC-2 0.25mmX60M df=1.4um 1010-19166	133,000	149,000	-	-	-	-	-	-	-	-	-	-	-
68-0329-23	InertCap AQUATIC-2 0.32mmX30M df=1.8um 1010-19247	96,000	108,000	-	-	-	-	-	-	-	-	-	-	-
68-0329-24	InertCap AQUATIC-2 0.32mmX60M df=1.8um 1010-19267	147,000	164,000	-	-	-	-	-	-	-	-	-	-	-
68-0329-25	InertCap AQUATIC-2 0.53mmX30M df=3.0um 1010-19448	112,000	125,000	-	-	-	-	-	-	-	-	-	-	-
68-0329-26	InertCap AQUATIC-2 0.53mmX75M df=3.0um 1010-19478	199,000	222,000	-	-	-	-	-	-	-	-	-	-	-
68-0330-66	InertCap AQUATIC 0.25mm X 30M df=1.0um 1010-29145	85,000	94,800	-	-	-	-	-	-	-	-	-	-	-
68-0330-67	InertCap AQUATIC 0.25mm X 60M df=1.0um 1010-29165	133,000	148,000	-	-	-	-	-	-	-	-	-	-	-
68-0330-68	InertCap AQUATIC 0.32mm X 60M, df=1.4um 1010-29266	147,000	164,000	-	-	-	-	-	-	-	-	-	-	-
68-0330-69	InertCap AQUATIC 0.53mm X 75M, df=2.0um 1010-29477	199,000	222,000	-	-	-	-	-	-	-	-	-	-	-
68-0334-33	INERTCAP PJURE-WAX 0.18MM X 20M DF=0.18 1010-68031	64,000	74,200	-	-	-	-	-	-	-	-	-	-	-
68-0334-34	INERTCAP PJURE-WAX 0.18MM X 40M DF=0.18 1010-68051	121,000	139,000	-	-	-	-	-	-	-	-	-	-	-
68-0334-35	INERTCAP PJURE-WAX 0.25MM LD.X30M DF=0.25UM 1010-68142	76,000	85,500	-	-	-	-	-	-	-	-	-	-	-
68-0334-36	INERTCAP PJURE-WAX 0.25MMLD.X30M DF=0.5UM 1010-68144	76,000	85,500	-	-	-	-	-	-	-	-	-	-	-
68-0334-37	INERTCAP PJURE-WAX 0.25MM LD.X60M DF=0.25UM 1010-68162	135,000	152,000	-	-	-	-	-	-	-	-	-	-	-
68-0334-38	INERTCAP PJURE-WAX 0.25MMLD.X60M DF=0.5UM 1010-68164	135,000	152,000	-	-	-	-	-	-	-	-	-	-	-
68-0334-39	INERTCAP PJURE-WAX 0.32MM LD.X30M DF=0.25UM 1010-68242	81,000	91,700	-	-	-	-	-	-	-	-	-	-	-
68-0334-40	INERTCAP PJURE-WAX 0.32MMLD.X30M DF=0.5UM 1010-68244	81,000	91,700	-	-	-	-	-	-	-	-	-	-	-
68-0334-41	INERTCAP PJURE-WAX 0.32MM LD.X60M DF=0.25UM 1010-68262	143,000	162,000	-	-	-	-	-	-	-	-	-	-	-
68-0334-42	INERTCAP PJURE-WAX 0.32MMLD.X60M DF=0.5UM 1010-68264	143,000	162,000	-	-	-	-	-	-	-	-	-	-	-
68-0334-43	INERTCAP PJURE-WAX 0.53MM LD.X15M DF=1.00UM 1010-68425	51,000	56,700	-	-	-	-	-	-	-	-	-	-	-
68-0334-44	INERTCAP PJURE-WAX 0.53MM LD.X30M DF=1.00UM 1010-68445	93,000	103,000	-	-	-	-	-	-	-	-	-	-	-
68-0334-63	INERTCAP FOR AMINES 0.32MMLD. X 15M 1010-69229	59,000	64,000	-	-	-	-	-	-	-	-	-	-	-
68-0334-64	INERTCAP FOR AMINES 0.32MMLD. X 30M 1010-69249	102,000	110,000	-	-	-	-	-	-	-	-	-	-	-
68-0334-65	INERTCAP FOR AMINES 0.32MMLD. X 60M 1010-69269	171,000	183,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-27	Inertsil ODS-2 5um 4.0X100mm 5020-01120	65,000	69,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-28	Inertsil ODS-2 5um 2.1X150mm 5020-01121	72,000	76,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-29	Inertsil ODS-2 5um 3.0X150mm 5020-01122	72,000	76,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-30	Inertsil ODS-2 5um 4.0X150mm 5020-01123	72,000	76,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-31	Inertsil ODS-2 5um 4.6X150mm 5020-01124	72,000	76,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-32	Inertsil ODS-2 5um 2.1X250mm 5020-01125	82,000	87,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-33	Inertsil ODS-2 5um 3.0X250mm 5020-01126	82,000	87,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-34	Inertsil ODS-2 5um 4.0X250mm 5020-01127	82,000	87,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-35	Inertsil ODS-2 5um 4.6X250mm 5020-01128	82,000	87,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-78	Inertsil ODS-3 5um 4.6X150mm 5020-01731	58,000	61,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-79	Inertsil ODS-3 5um 4.6X250mm 5020-01732	67,000	71,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-88	Inertsil ODS-3 5um 4.6X 50mm 5020-01763	48,000	51,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-89	Inertsil ODS-3 5um 4.6X 75mm 5020-01764	53,000	56,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-90	Inertsil ODS-3 5um 4.6X100mm 5020-01765	53,000	56,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-93	Inertsil ODS-3 5um 4.6x125mm 5020-01768	58,000	61,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-94	Inertsil ODS-3 3um 4.6X 75mm 5020-01770	57,000	60,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-95	Inertsil ODS-3 3um 4.6X150mm 5020-01771	66,000	70,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-96	Inertsil ODS-3 3um 4.6X250mm 5020-01772	76,000	80,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-97	Inertsil ODS-3 3um 4.6X 50mm 5020-01774	51,000	54,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-98	Inertsil ODS-3 3um 4.6X100mm 5020-01775	57,000	60,000	-	-	-	-	-	-	-	-	-	-	-
68-0345-99	Inertsil ODS-3 3um 4.6x125mm 5020-01776	66,000	70,000	-	-	-	-	-	-	-	-	-	-	-
68-0353-06	Inertsil ODS-3 3um 4.6X 30mm 5020-04440	51,000	54,000	-	-	-	-	-	-	-	-	-	-	-
68-0353-07	Inertsil ODS-3 3um 4.6X 33mm 5020-04441	51,000	54,000	-	-	-	-	-	-	-	-	-	-	-
68-0353-70	Inertsil ODS-3 5um 4.6X 30mm 5020-04540	48,000	51,000	-	-	-	-	-	-	-	-	-	-	-
68-0353-71	Inertsil ODS-3 5um 4.6X 33mm 5020-04541	48,000	51,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-32	InertSustain C18 5um 3.0x 20mm 5020-07320	48,000	51,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-33	InertSustain C18 5um 3.0x 30mm 5020-07321	48,000	51,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-34	InertSustain C18 5um 3.0x 50mm 5020-07322	48,000	51,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-35	InertSustain C18 5um 3.0x 75mm 5020-07323	53,000	56,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-36	InertSustain C18 5um 3.0x100mm 5020-07324	53,000	56,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-37	InertSustain C18 5um 3.0x150mm 5020-07325	58,000	61,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-38	InertSustain C18 5um 3.0x250mm 5020-07326	67,000	71,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-39	InertSustain C18 5um 3.0x125mm 5020-07327	58,000	61,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-48	InertSustain C18 5um 4.6x 20mm 5020-07340	48,000	51,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-49	InertSustain C18 5um 4.6x 30mm 5020-07341	48,000	51,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-50	InertSustain C18 5um 4.6x 50mm 5020-07342	48,000	51,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-51	InertSustain C18 5um 4.6x 75mm 5020-07343	53,000	56,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-52	InertSustain C18 5um 4.6x100mm 5020-07344	53,000	56,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-53	InertSustain C18 5um 4.6x150mm 5020-07345	58,000	61,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-54	InertSustain C18 5um 4.6x250mm 5020-07346	67,000	71,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-55	InertSustain C18 5um 4.6x200mm 5020-07347	67,000	71,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-56	InertSustain C18 5um 4.6x125mm 5020-07348	58,000	61,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-75	InertSustain C18 3um 3.0x 20mm 5020-07420	51,000	54,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-76	InertSustain C18 3um 3.0x 30mm 5020-07421	51,000	54,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-77	InertSustain C18 3um 3.0x 50mm 5020-07422	51,000	54,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-78	InertSustain C18 3um 3.0x 75mm 5020-07423	57,000	60,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-79	InertSustain C18 3um 3.0x100mm 5020-07424	57,000	60,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-80	InertSustain C18 3um 3.0x150mm 5020-07425	66,000	70,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-81	InertSustain C18 3um 3.0x250mm 5020-07426	76,000	80,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-82	InertSustain C18 3um 3.0x125mm 5020-07427	66,000	70,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-91	InertSustain C18 3um 4.6x 20mm 5020-07440	51,000	54,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-92	InertSustain C18 3um 4.6x 30mm 5020-07441	51,000	54,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-93	InertSustain C18 3um 4.6x 50mm 5020-07442	51,000	54,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-94	InertSustain C18 3um 4.6x 75mm 5020-07443	57,000	60,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-95	InertSustain C18 3um 4.6x100mm 5020-07444	57,000	60,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-96	InertSustain C18 3um 4.6x150mm 5020-07445	66,000	70,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-97	InertSustain C18 3um 4.6x250mm 5020-07446	76,000	80,000	-	-	-	-	-	-	-	-	-	-	-
68-0361-98	InertSustain C18 3um 4.6x125mm 5020-07447	66,000	70,000	-	-	-	-	-	-	-	-	-	-	-
68-0366-90	Inertsil ODS-2 5um 1.0 X 150mm 5020-13103	85,000	90,000	-	-	-	-	-	-	-	-	-	-	-
68-0366-91	Inertsil ODS-2 5um 1.0 X 250mm 5020-13105	98,000	103,000	-	-	-	-	-	-	-	-	-	-	-
68-0366-92	Inertsil ODS-2 5um 1.5 X 150mm 5020-13153	85,000	90,000	-	-	-	-	-	-	-	-	-	-	-
68-0366-93	Inertsil ODS-2 5um 1.5 X 250mm 5020-13155	98,000	103,000	-	-	-	-	-	-	-	-	-	-	-
68-0399-37	Inertsil ODS-3 5um 4.6X300mm 5020-87011	72,000	76,000	-	-	-	-	-	-	-	-	-	-	-
68-0399-59	InertSustain C18 5um 4.6X300mm 5020-87033	72,000	76,000	-	-	-	-	-	-	-	-	-	-	-
68-0420-43	Inertsil ODS-2 5um 3.0X125mm 5020-89966	72,000	76,000	-	-	-	-	-						

品番	商品名	旧価格	新価格	研究用総合 機種2023 頁	サンクアス ト 2023 頁	ナビス2024 頁	サニーフーズ 2024 頁	設備2024 頁	アズビエア 2023 頁	アズツール 2021 頁	ナビ助2023 頁	産産産育養 用品パンフ 頁	ウェルビー イングパン フ 頁	サイエンス カタログ 頁
6-968-02	デュボン(TM)タイプベック(R)製 白衣 M 4250-M	1,560	1,770	2952	2952									
6-968-03	デュボン(TM)タイプベック(R)製 白衣 LL 4250-LL	1,560	1,770	2952	2952									
6-969-01	デュボン(TM)タイプベック(R)製 フード付ジャンパー M 2010B-L	1,280	1,400	2952	2952									
6-969-02	デュボン(TM)タイプベック(R)製 フード付ジャンパー M 2010B-M	1,280	1,400	2952	2952									
6-969-03	デュボン(TM)タイプベック(R)製 フード付ジャンパー LL 2010B-LL	1,280	1,400	2952	2952									
6-971-01	デュボン(TM)タイプベック(R)製 スボン L 3580-L	1,340	1,480	2952	2952									
6-971-02	デュボン(TM)タイプベック(R)製 スボン M 3580-M	1,340	1,480	2952	2952									
6-971-03	デュボン(TM)タイプベック(R)製 スボン LL 3580-LL	1,340	1,480	2952	2952									
6-972-01	デュボン(TM)タイプベック(R)製キャップ(大) 10枚入 6621	2,650	3,010	2952	2952									
6-972-02	デュボン(TM)タイプベック(R)製キャップ(小) 10枚入 6611	1,860	2,120	2952	2952									
6-973-01	デュボン(TM)タイプベック(R)製シューズカバー フリーサイズ(10双入) 6862	3,160	3,580	2952	2952									
6-973-02	デュボン(TM)タイプベック(R)製アームカバー (10双入) 6702	3,160	3,580	2952	2952									
7-1025-01	ガラス ディスポボックス A 6個入 12-009-7A	13,000	14,900	2778	2778									
7-1025-02	ガラス ディスポボックス B 6個入 12-009-7B	10,500	12,100	2778	2778									
7-1045-31	グリーン温風循環器 640×605×1385mm CHD-200AS	588,000	598,000	2715	2715									
7-1108-32	イージースロー KES-01	13,000	10,000			1788					326			
7-1129-01	ポケットLED検眼鏡・耳鏡セット ブラック 92871-BLK	58,500	64,400		781									
7-1129-02	ポケットLED検眼鏡・耳鏡セット ホワイト 92871-WHT	58,500	64,400		781									
7-1129-03	ポケットLED検眼鏡・耳鏡セット パープル 92871-PUR	58,500	64,400		781									
7-1129-04	ポケットLED検眼鏡・耳鏡セット スカイブルー 92871-BLU	58,500	64,400		781									
7-1129-12	リニューザブルスベキユラ4種(各1個)・ディスポーザブルスベキユラ9個 21103-U	2,200	2,600		781									
7-1130-01	ポケットLED検眼鏡 ブラック 12870-BLK	33,800	37,200		781									
7-1130-02	ポケットLED検眼鏡 ホワイト 12870-WHT	33,800	37,200		781									
7-1130-03	ポケットLED検眼鏡 パープル 12870-PUR	33,800	37,200		781									
7-1130-04	ポケットLED検眼鏡 スカイブルー 12870-BLU	33,800	37,200		781									
7-1131-01	ポケットLED耳鏡 ブラック 2.9ルーメン 22870-BLK	25,900	28,500		781									
7-1131-02	ポケットLED耳鏡 ホワイト 2.9ルーメン 22870-WHT	25,900	28,500		781									
7-1131-03	ポケットLED耳鏡 パープル 2.9ルーメン 22870-PUR	25,900	28,500		781									
7-1131-04	ポケットLED耳鏡 スカイブルー 2.9ルーメン 22870-BLU	25,900	28,500		781									
7-1132-01	ポケットLEDセット ブラック 92880-BLK	77,700	85,500		781									
7-1132-02	ポケットLEDセット ホワイト 92880-WHT	77,700	85,500		781									
7-1132-03	ポケットLEDセット パープル 92880-PUR	77,700	85,500		781									
7-1132-04	ポケットLEDセット スカイブルー 92880-BLU	77,700	85,500		781									
7-1132-11	ポケットLED用ハードケース 723528	9,000	9,900		781									
7-1133-01	ポケットLED検眼鏡 ブラック 12880-BLK	45,000	49,500		781									
7-1133-02	ポケットLED検眼鏡 ホワイト 12880-WHT	45,000	49,500		781									
7-1133-03	ポケットLED検眼鏡 パープル 12880-PUR	45,000	49,500		781									
7-1133-04	ポケットLED検眼鏡 スカイブルー 12880-BLU	45,000	49,500		781									
7-1134-01	ポケットLED耳鏡 ブラック 5.5ルーメン 22880-BLK	32,700	36,000		781									
7-1134-02	ポケットLED耳鏡 ホワイト 5.5ルーメン 22880-WHT	32,700	36,000		781									
7-1134-03	ポケットLED耳鏡 パープル 5.5ルーメン 22880-PUR	32,700	36,000		781									
7-1134-04	ポケットLED耳鏡 スカイブルー 5.5ルーメン 22880-BLU	32,700	36,000		781									
7-1184-01	サウナマット(スレン染め) 410×485 1袋(10枚入) KY142TAS-BR	8,940	9,170									141		
7-1184-12	サウナマット(スレン染め) 700×1300 1袋(10枚入) KY650TAS-BR	26,800	32,400									141		
7-1367-21	自動血圧計99×201×123mm HBP-1320	24,800	26,000	3106	3106	699								
7-1409-01	お風呂洗い場マット ピンク AF-09	4,800	6,980									139		
7-1409-02	お風呂洗い場マット グリーン AF-10	4,800	6,980									139		
7-2053-01	バスタオル 1袋(12枚入) OK800W	5,400	5,870									148		
7-2592-01	アクティ テープ止めタイプ ベーシックケア 1袋(20枚入) S	2,500	3,200									111		
7-2592-02	アクティ テープ止めタイプ ベーシックケア 1袋(20枚入) M	2,500	3,200									111		
7-2592-03	アクティ テープ止めタイプ ベーシックケア 1袋(17枚入) L	2,500	3,200									111		
7-2593-01	アクティラジ型ハンツベシックケア 1袋(20枚入) M	1,800	2,160									111		
7-2593-02	アクティラジ型ハンツベシックケア 1袋(18枚入) L	1,800	2,160									111		
7-2902-08	ナビス駆血帯 ラベンダー 金具セット	830	920			1269								
7-2902-09	ナビス駆血帯 ミント 金具セット	830	920			1269								
7-2903-08	ナビス駆血帯 替えチューブ ラベンダー 400mm	260	300			1269								
7-2903-09	ナビス駆血帯 替えチューブ ミント 400mm	260	300			1269								
7-2904-08	ナビス駆血帯 替えチューブ ラベンダー 1m	520	590			1269								
7-2904-09	ナビス駆血帯 替えチューブ ミント 1m	520	590			1269								
7-2994-01	LED耳鏡 250-2	46,500	51,200		781									
7-2995-01	マクロビュー ベーシック 238-2	53,900	59,300		780									
7-2995-02	マクロビュー プラス 238-3	67,500	74,300		780									
7-2995-11	iExaminer キット 11840-IEX	11,300	12,500		780									
7-2995-12	ルミビュークリアスベキユラ 2.75mm 680個入 52432-CLR-2	8,500	9,400		780									
7-2995-13	ルミビュークリアスベキユラ 4.25mm 680個入 52434-CLR-2	8,500	9,400		780									
7-2995-14	ハンドルセット USB充電器付 719-3	67,500	74,300		780									
7-2995-15	ユニバーサルデスクチャージャー 719-DSK-J	45,000	49,500		780									
7-3070-01	検眼鏡 ハンコプティック ベーシック 118-2	136,000	149,600		780									
7-3070-02	検眼鏡 ハンコプティック プラス 118-3	153,000	168,300		780									
7-3070-11	検眼鏡 ハンコプティック 専用アイカップ 5個入 118-EC	6,200	6,900		780									
7-3080-01	ユニバーサルデスクチャージャー リチウムハンドル2本付 71-xxxLDE-J	146,300	161,000		784									
7-3239-01	検眼鏡 2.5Vファイバーオプティックハンドル LEDタイプ 60813-LED	33,800	37,200		968									
7-3239-02	検眼鏡 2.5Vファイバーオプティックハンドル LEDタイプ 60814-LED	33,800	37,200		968									
7-3870-01	オムロン上腕式血圧計 HEM-8731	13,500	14,200		698									
7-3982-02	精製水 18L P18L	3,120	3,810		359									
7-4511-01	松葉杖ラック(アルミ製) スタンド型	47,000	50,000		1852									
7-4511-02	松葉杖ラック(アルミ製) 吊り型	57,800	64,100		1852									
7-4521-01	救急カート レッド AM930-R	157,000	165,000		941									
7-4521-11	救急カート 仕切板小ヨコ(1枚)	1,100	1,200		941									
7-4521-12	救急カート 仕切板小タテ(1枚)	1,100	1,200		941									
7-4522-01	調剤ユニット(スライドタイプ) 上置き調剤リレー型タイプ V930-10YT	179,000	188,000		27									
7-4522-02	調剤ユニット(スライドタイプ) 下置き3枚引戸タイプ V965-09TS	194,000	204,000		27									
7-4522-12	調剤ユニット(スライドタイプ) V965用ベース V965-B1	32,800	35,000		27									
7-4522-13	調剤ユニット(スライドタイプ) ユニット用天板 V965-WT1	40,500	47,000		27									
7-4593-02	口腔ケアモデル セイケツくん	78,000	80,000								353			
7-4800-01	ERBE 高周波手術装置 本体 (VIO50C) E120978	800,000	880,000			1612								
7-4800-02	ERBE 高周波手術装置 本体 (VIO100C) E120977	920,000	1,000,000			1612								
7-4800-11	ERBE 高周波手術装置用オプシオン 2ペダルフットスイッチ E120979	125,000	131,000			1612								
7-4800-20	ERBE 高周波手術装置用オプシオン ハイポラーケーブル E120688	32,500	36,000			1612								
7-5148-01	油性マーカーライン 極細・細字 黒 PM-41D	140	150									261		
7-5148-02	油性マーカーライン 極細・細字 赤 PM-41R	140	150									261		
7-5148-03	油性マーカーライン 極細・細字 青 PM-41B	140	150									261		
7-5153-01	修正テープ(ケンシタ)代替テープ幅4mm TW-284	280	290									261		
7-5153-02	修正テープ(ケンシタ)代替テープ幅5mm TW-285	280	290									261		
7-5153-03	修正テープ(ケンシタ)代替テープ幅6mm TW-286	280	290									261		
7-5154-01	なめらかボールペンK2マッハボールノック式黒10本 K2PR-NB207DX10	1,000	1,010									261		
7-5154-02	なめらかボールペンK2マッハボールノック式黒10本 K2PR-NB207RX10	1,000	1,010									261		
7-5154-03	なめらかボールペンK2マッハボールノック式青10本 K2PR-NB207BX10	1,000	1,010									261		
7-5155-01	K2ボールペン マッハボール ノック式替芯 黒5本 K2PRR-NB207DX5	350	360									261		
7-5155-02	K2ボールペン マッハボール ノック式替芯 赤5本 K2PRR-NB207RX5	350	360									261		
7-5160-02	用箋挿B(総クロス貼) A4 ヨコヨハ-23	520	530									261		
7-5162-01	用箋挿B(総クロス貼) A3 タテヨハ-48	820	850									261		
7-5162-02	用箋挿B(総クロス貼) A3 ヨコヨハ-43	820	830									261		
7-5163-02	用箋挿B(総クロス貼) B4 ヨコヨハ-24	670	700									261		
7-5165-01	用箋挿B(総クロス貼) B6 タテヨハ-27N	400	410									261		
7-5165-02	用箋挿B(総クロス貼) B6 ヨコヨハ-22N	400	410									261		
7-5172-01	チューブファイル<エ>青A4縦青幅75mm 7-E660B	1,420	1,430	2608	2608									
7-5172-02	チューブファイル<エ>シルバA4縦青幅													

品番	商品名	旧価格	新価格	研究用総合 機電2023 頁	サンクス 2023 頁	ナビス2024 頁	サニーフーズ 2024 頁	設備2024 頁	アズビエア 2023 頁	アズテール 2021 頁	ナビ助2023 頁	産産産育養 用品/パンフ 頁	ウェルビー イング/パン フ 頁	サイエンス カタログ 頁
8-3915-21	ドクターズツール 本体 LS-009GS	115,000	120,000			1561								
8-4038-01	ニューラポロチクタ W型	12,700	15,000	3005	3005									
8-4038-02	ニューラポロチクタ S型	7,670	9,900	3005	3005									
8-4038-04	ニューラポロチクタ W型(挿入口付き)	15,200	18,700	3005	3005									
8-4386-21	電子血圧計(上腕式) HEM-8712	8,100	8,500	3106	3106	698								
8-4517-01	次亜塩素酸ナトリウム製剤(殺菌剤漂白剤)1000mL	1,320	1,400	2670	2670	368					431			
8-4517-02	次亜塩素酸ナトリウム製剤(殺菌剤漂白剤)20kg	6,600	6,900	2670	2670	368								396
8-4684-01	注射台(車椅子対応型) NVS-WC	42,400	46,000			1260								396
8-4891-11	手薬個人ケースII(ワンタッチ) ブルー 10枚入 DC-BL	760	980			278								504
8-4891-12	手薬個人ケースII(ワンタッチ) レッド 10枚入 DC-RD	760	980			278								504
8-4891-13	手薬個人ケースII(ワンタッチ) グリーン 10枚入 DC-GR	760	980			278								504
8-4891-14	手薬個人ケースII(ワンタッチ) グレー 10枚入 DC-GY	760	980			278								504
8-4924-05	収納ユニット(薄型タイプ) 上下兼用 オープンタイプ V930-10K	48,000	50,000			26								
8-4924-06	収納ユニット(薄型タイプ) 下置き専用 2枚引き戸タイプ V930-11S	63,200	66,000			26								
8-4924-07	収納ユニット(薄型タイプ) 下置き専用 両開きタイプ V930-11H	67,200	71,000			26								
8-4924-08	収納ユニット(薄型タイプ) 下置き専用 両開き・窓付タイプ V930-11HG	94,200	99,000			26								
8-4924-09	収納ユニット(薄型タイプ) 下置き専用 両開き・ハイタイプ V930-21H	107,100	113,000			26								
8-4924-10	収納ユニット(薄型タイプ) V930用ベース V930-B1	12,500	13,000			26								
8-4924-11	収納ユニット(薄型タイプ) 天袋 両開き・高さ400mm V930-04H	52,000	55,000			26								
8-4924-12	収納ユニット(薄型タイプ) 天袋 両開き・高さ500mm V930-05H	56,600	59,000			26								
8-4924-13	収納ユニット(薄型タイプ) 上部カバー 900×310×65~115mm V930-07A	24,200	25,000			26								
8-4924-14	収納ユニット(薄型タイプ) 上部カバー 900×310×105~195mm V930-11A	24,900	26,000			26								
8-4924-15	収納ユニット(薄型タイプ) 上部カバー 900×310×165~305mm V930-17A	25,600	27,000			26								
8-4924-21	収納ユニット(薄型タイプ) 上置き専用 2枚引き戸タイプ V930-10S	63,000	66,000			26								
8-4924-22	収納ユニット(薄型タイプ) 上置き専用 両開きタイプ V930-10H	67,000	71,000			26								
8-4924-23	収納ユニット(薄型タイプ) 上置き専用 2枚引き戸・窓付タイプ V930-10SG	85,000	89,000			26								
8-4924-24	収納ユニット(薄型タイプ) 上置き専用 両開き・窓付タイプ V930-10HG	95,000	99,000			26								
8-5361-01	ラボマット 760mm×44mm×0.91mm 14-203A	6,900	7,900	3006	3006									
8-5361-02	ラボマット 760mm×30mm×0.91mm 14-203B	41,500	47,500	3006	3006									
8-5573-02	ライト[ストリームライト(R)プロポリマーシリーズ] SL68202YEL 4AA LED	9,400	11,000			553								
8-5573-03	ライト[ストリームライト(R)プロポリマーシリーズ] SL33202YEL 3C LED	13,000	14,000			553								
8-5881-01	卓上クリーンベンチ HCB-900	515,000	543,000	1130	1130	226								
8-5881-02	卓上クリーンベンチ HCB-1200	643,000	653,000	1130	1130	226								
8-5881-03	卓上クリーンベンチ HCB-900G	535,000	564,000	1130	1130									
8-5881-04	卓上クリーンベンチ HCB-1200G	663,000	674,000	1130	1130									
8-5884-01	ヨーロッパカードII(補助天板付き・回診タイプ) 2段ブルー 630×400×855mm ES-B2B	80,000	93,000			92								
8-5884-02	ヨーロッパカードII(補助天板付き・回診タイプ) 2段ピンク 630×400×855mm ES-B2P	80,000	93,000			92								
8-5884-03	ヨーロッパカードII(補助天板付き・回診タイプ) 5段ブルー 630×400×855mm ES-B5B	95,500	108,000			92								
8-5884-04	ヨーロッパカードII(補助天板付き・回診タイプ) 5段ピンク 630×400×855mm ES-B5P	95,500	108,000			92								
8-5915-01-20	ストップウォッチ 校正証明書付 PC396	7,250	7,350	2530	2530									532
8-5960-01-20	ストップウォッチ 校正証明書付 PC894	7,900	8,000	2531	2531	2043								532
8-614-01	コンパクトクリーンベンチ・プラス BH900-ADL	510,000	540,000			227								
8-614-02	コンパクトクリーンベンチ・プラス BH1200-ADL	630,000	660,000			227								
8-6340-01	インプロバール消毒液50%(カネイチ) 500mL	530	540			358								
8-6340-02	インプロバール消毒液50%(カネイチ) 2L	1,870	2,000			358								
8-6340-03	インプロバール消毒液50%(カネイチ) 5L(コック付き)	4,500	4,800			358								
8-6341-01	インプロバール消毒液70%(カネイチ) 500mL	630	650			358							422	
8-6341-03	インプロバール消毒液70%(カネイチ) 5L(コック付き)	5,600	5,850			358							422	
8-6342-01	消毒用エタノールα(アルファ) (カネイチ) 500mL	730	850			357							422	
8-6342-02	消毒用エタノールα(アルファ) (カネイチ) 2L	2,900	3,300			357							422	
8-6342-03	消毒用エタノールα(アルファ) (カネイチ) 5L(コック付き)	7,100	8,100			357							422	
8-6344-01	手指消毒剤カネバス 500mL	2,540	2,700			316								
8-6344-02	手指消毒剤カネバス 1L	4,410	4,750			316								
8-6344-03	手指消毒剤カネバス 5L	16,900	18,000			316								
8-6346-11	クロルヘキシジンアルコール消毒液5%(カネイチ) 500ml	2,050	2,170			359								
8-6347-01	ベンザルコニウム塩化物消毒液10%(日本薬局方) 500mL	680	780			358							422	
8-6363-01	滅菌ゲル(超音波検査用) 1箱(20mL/個×48個入) TK001	14,400	19,200			808								
8-6382-01	色覚検査表 石原色覚検査表II コンサシズ版14表 1205C	12,000	14,000			799								
8-6382-02	色覚検査表 石原色覚検査表II 24表 1205B	18,000	20,000			799								
8-6382-03	色覚検査表 石原色覚検査表II 国際版38表 1205A	20,000	22,000			799								
86-6716-28	p53 (Ab-15) Antibody 100ul 21085	120,000	109,000	1781	1781									
86-7114-61	Recombinant Human Synaptosomal-associated protein 25 (SNAP25) 100ug AP70787	107,000	113,000	1774	1774									
86-7167-92	Recombinant Rotavirus A Outer capsid protein VP4,partial 100ug AP72893	221,000	234,000	1774	1774									
86-7170-58	Recombinant Escherichia coli protein FimH (fimH) 100ug AP72985	221,000	234,000	1774	1774									
86-7187-42	Recombinant Human Leukemia inhibitory factor protein (LIF) (Active) 100ug AP73519	267,000	283,000	1774	1774									
86-7194-54	Recombinant Epstein-Barr virus Small capsomere-interacting protein (SCP), partial 100ug AP73694	194,000	206,000	1774	1774									
86-7201-97	Recombinant Human NAD-dependent protein deacetylase sirtuin-1 (SIRT1) 100ug AP73960	107,000	113,000	1774	1774									
86-7254-47	Recombinant Human Ketohexokinase (KHK (C-6His) 50ug AP75561	123,000	55,000	1774	1774									
86-7318-82	Recombinant Human Calreticulin (CALR) 100ug AP77380	107,000	113,000	1774	1774									
86-7319-13	Recombinant Human Tropomyosin alpha-3 chain (TPM3) 100ug AP77390	107,000	113,000	1774	1774									
86-7621-29	3-oxo-5-alpha-steroid 4-dehydrogenase 1 100ug AP87749	230,000	244,000	1774	1774									
8-7045-01	ヨード染色剤(10%ハイポアルコール) 500mL	2,160	2,500			359								
8-7092-01	バイタルナビ血圧計 ネイビーブルー LB成人用	9,200	9,800			666							427	
8-7092-02	バイタルナビ血圧計 グレー LB成人用	9,200	9,800			666							427	
8-7092-03	バイタルナビ血圧計 マゼンタ LB成人用	9,200	9,800			666							427	
8-7092-04	バイタルナビ血圧計 ブラック LB成人用	9,200	9,800			666							427	
8-7092-05	バイタルナビ血圧計 ピンク LB成人用	9,200	9,800			666							427	
8-7092-06	バイタルナビ血圧計 スカイブルー LB成人用	9,200	9,800			666							427	
8-7092-07	バイタルナビ血圧計 スカイブルー LB小児用	9,200	9,800			666							427	
8-7093-01	バイタルナビ血圧計(ラテックスフリー) ネイビーブルー LF成人用	10,200	11,000			666							427	
8-7093-02	バイタルナビ血圧計(ラテックスフリー) グレー LF成人用	10,200	11,000			666							427	
8-7093-03	バイタルナビ血圧計(ラテックスフリー) マゼンタ LF成人用	10,200	11,000			666							427	
8-7093-04	バイタルナビ血圧計(ラテックスフリー) ブラック LF成人用	10,200	11,000			666							427	
8-7093-05	バイタルナビ血圧計(ラテックスフリー) ピンク LF成人用	10,200	11,000			666							427	
8-7093-06	バイタルナビ血圧計(ラテックスフリー) スカイブルー LF成人用	10,200	11,000			666							427	
8-7093-07	バイタルナビ血圧計(ラテックスフリー) スカイブルー LF小児用	10,200	11,000			666							427	
8-7486-11	アネロイド血圧計(チュラショック・ハンド型) 成人用(中) カフ付き DS58-11	39,500	43,500			671								
8-7486-21	アネロイド血圧計(チュラショック・ハンド型) ゲージのみ DS58	32,500	35,800			671								
8-7487-02	アネロイド血圧計(チュラショック・ボケット型) ゲージのみ(レーザー刻印) DS48A	34,900	38,400			669								
8-7487-25	DS44チューブアダプタ送気球付き 1DSLC	2,100	2,400			669								
8-7487-26	フレックスポート用アクセサリ[DS44・45・48用] DS45チューブアダプタ送気球付き(小) 1DSAS	3,100	3,500			669								
8-7487-27	DS45チューブアダプタ送気球付き(大) 1DSAL	3,900	4,300			669								
8-7487-28	洗浄用カフポートブラグ(フレックスポートカフ用) 5082-159	900	1,000			669								
8-7546-01	アネロイド血圧計(チュラショック・ハンド型) TR-1型 成人用(中) カフ付き 5098-27	29,100	32,100			671								
8-7546-02	アネロイド血圧計(チュラショック・ハンド型) TR-1型 小児用(中) カフ付き 5098-29	28,600	31,500			671								
8-7546-11	アネロイド血圧計(チュラショック・ハンド型) TR-1型 ゲージのみ 5098-31	23,300	25,700			671								
8-7574-01	フレックスポートリニューザブルカフ 新生児用 チューブなし REUSE-06	3,900	4,300			670								
8-7574-02	フレックスポートリニューザブルカフ 乳幼児用 チューブなし REUSE-07	4,100	4,600			670								
8-7574-03	フレックスポートリニューザブルカフ 小児用(小) チューブなし REUSE-08	4,300	4,800			670								
8-7574-04	フレックスポートリニューザブルカフ 小児用(中) チューブなし REUSE-09	4,500	5,000			670								
8-7574-05	フレックスポートリニューザブルカフ 成人用(小) チューブなし REUSE-10	4,800	5,300			670								
8-7574-06	フレックスポートリニューザブルカフ 成人用(中) チューブなし REUSE-11	5,000	5,500			670								
8-7574-														

品番	商品名	旧価格	新価格	研究用総合 機織2023 頁	サンクアス ト 2023 頁	ナビス2024 頁	サニーフ ーズ 2024 頁	設備2024 頁	アズビエ ア 2023 頁	アズツール 2021 頁	ナビ助2023 頁	感染症対策 用品パンフ 頁	ウェルビー イングパン フ 頁	サイエンス カタログ 頁
8-7699-01	フレックスポート(TM)リユーズバルカフ カフチューブ・乳幼児用 REUSE-07-2TPE	4,300	4,800			670								
8-7699-02	フレックスポート(TM)リユーズバルカフ カフチューブ・小児用(小) REUSE-08-2TPE	4,500	5,000			670								
8-7699-03	フレックスポート(TM)リユーズバルカフ カフチューブ・小児用(中) REUSE-09-2TPE	4,800	5,300			670								
8-7699-04	フレックスポート(TM)リユーズバルカフ カフチューブ・成人用(小) REUSE-10-2TPE	5,000	5,500			670								
8-7699-05	フレックスポート(TM)リユーズバルカフ カフチューブ・成人用(中) REUSE-11-2TPE	5,200	5,800			670								
8-7699-06	フレックスポート(TM)リユーズバルカフ カフチューブ・成人用(大) REUSE-12-2TPE	5,400	6,000			670								
8-7699-07	フレックスポート(TM)リユーズバルカフ カフチューブ・大腿部用 REUSE-13-2TPE	9,000	9,900			670								
8-7751-01	フレックスポート(TM)リユーズバルカフ カフチューブ・小児用(小) REUSE-08-1SC	4,500	5,000			670								
8-7751-02	フレックスポート(TM)リユーズバルカフ カフチューブ・小児用(中) REUSE-09-1SC	4,800	5,300			670								
8-7751-03	フレックスポート(TM)リユーズバルカフ カフチューブ・成人用(小) REUSE-10-1SC	5,000	5,500			670								
8-7751-04	フレックスポート(TM)リユーズバルカフ カフチューブ・成人用(中) REUSE-11-1SC	5,200	5,800			670								
8-7751-05	フレックスポート(TM)リユーズバルカフ カフチューブ・成人用(大) REUSE-12-1SC	5,400	6,000			670								
8-7751-06	フレックスポート(TM)リユーズバルカフ カフチューブ・大腿部用 REUSE-13-1SC	9,000	9,900			670								
8-7786-01	フレックスポートディスポカフ(20枚入) SOFT06	22,500	23,700			670								
8-7786-02	フレックスポートディスポカフ(20枚入) SOFT-07	22,500	23,700			670								
8-7786-03	フレックスポートディスポカフ(20枚入) SOFT08	22,500	23,700			670								
8-7786-04	フレックスポートディスポカフ(20枚入) SOFT-09	22,500	23,700			670								
8-7786-05	フレックスポートディスポカフ(20枚入) SOFT-10	32,100	33,800			670								
8-7786-06	フレックスポートディスポカフ(20枚入) SOFT-11	32,100	33,800			670								
8-7786-07	フレックスポートディスポカフ(20枚入) SOFT-12	32,100	33,800			670								
8-7786-08	フレックスポートディスポカフ(20枚入) SOFT13	42,800	45,000			670								
8-7814-01	Aネロイド血圧計(デュラショック・ゲージ一体型高精度) ゲージのみ DS45	11,500	12,700			669								
8-7953-01	フレックスポート用1チューブ ロング10本 1-TPS	3,300	3,700			669								
8-7953-02	フレックスポート用2チューブ ルアー10本 2-SRC	4,400	4,900			669								
8-7953-03	フレックスポート用2チューブロング10本 2-TPSE	4,400	4,900			669								
8-7953-04	フレックスポート用1チューブネジ式10本 1-SC	4,400	4,900			669								
8-7955-04	フレックスポート用アクセサリ[DS44・45・48用] DS48チューブアダプタ送気球付き(中) 1SRCS	3,100	3,500			669								
8-7955-05	フレックスポート用アクセサリ[DS44・45・48用] DS48チューブアダプタ送気球付き(大) 1SRCL	3,900	4,300			669								
8-7955-11	エア-リリースバルブ付き送気球(中) 5088-01	3,600	4,000			669								
8-7984-01	ディスポーザブル直線鏡管 φ19×250mm 1箱(25本×4袋入) 53130	64,600	71,100			1661								
8-7984-02	ディスポーザブル肛門鏡管 φ19×100mm 1箱(25本×4袋入) 53110	39,500	43,500			1661								
8-7984-11	3.5Vニッカド充電式ハンドル T1000-C	30,800	33,900			784								
8-8026-01	グリーンズベックディスポーザブル鏡鏡(590シリーズ) 小(白) 24本×4箱入 59000	29,300	32,300			1657								
8-8026-02	グリーンズベックディスポーザブル鏡鏡(590シリーズ) 中(グリーン) 24本×4箱入 59001	29,300	32,300			1657								
8-8026-03	グリーンズベックディスポーザブル鏡鏡(590シリーズ) 大(ブルー) 18本×4箱入 59004	40,500	44,600			1657								
8-8026-06	グリーンズベックディスポーザブル鏡鏡(590シリーズ) 特小(イエロー) 24本×4箱) 590XS	33,800	37,200			1657								
8-8244-01	ソフティヤーチップ(エリート・ハーバー-DLX用) L ブラック 1組(2個入) 5079-336	2,100	2,500			660								
8-8244-05	ソフティヤーチップ(エリート・ハーバー-DLX用) L グレー 1組(2個入) 5079-233	2,100	2,500			660								
8-8244-06	ソフティヤーチップ(エリート・ハーバー-DLX用) S グレー 1組(2個入) 5079-314	2,100	2,500			660								
8-8245-01	ソフティヤーチップ(プロフェッショナル用) L ブラック 1組(2個入) 5079-366	2,100	2,500			660								
8-8245-05	ソフティヤーチップ(プロフェッショナル用) L グレー 1組(2個入) 5079-170	2,100	2,500			660								
8-8245-06	ソフティヤーチップ(プロフェッショナル用) S グレー 1組(2個入) 5079-313	2,100	2,500			660								
8-8607-01	フタラール消毒液0.55%(メタル) 5L	13,000	13,500			1536								
8-8779-11	空気殺菌灯交換用殺菌ランプ 15W GL15(交換用殺菌ランプ)	2,500	3,750			352					391			
8-8779-12	空気殺菌灯交換用殺菌ランプ 30W GL30(交換用殺菌ランプ)	3,700	5,550			352					391			
8-8869-01	訪問看護用3ウェイバッグ(デオドラントフィルム内装) 59108	22,500	24,000			931					511			
89-0062-74	フェノールフタレイン溶液 pH測定用 IN 100mL 45000303	1,800	1,900	1799	1799									
89-0062-75	フェノールフタレイン溶液 pH測定用 IN 500mL 45000315	3,000	3,200	1799	1799									
89-0062-79	1W/V% フェノールフタレイン溶液 測定用 IN 100mL 45002363	2,000	2,500	1799	1799									
89-0062-80	1W/V% フェノールフタレイン溶液 測定用 IN 500mL 45002375	3,000	3,700	1799	1799									
89-0065-22	酸化マグネシウム 軽質 CP 500g 13000335	3,500	4,300	-	-									
89-0065-66	パラフィン(48-50℃) 一級 500g 16000365	2,700	2,800	2397	2397									
89-0065-67	パラフィン(54-56℃) 一級 500g 16000395	2,700	2,800	2397	2397									
89-0065-68	パラフィン(56-58℃) 一級 500g 16000405	2,700	2,800	2397	2397									
89-0065-69	パラフィン(58-60℃) 一級 500g 16000415	4,300	4,400	2397	2397									
89-0065-70	流動パラフィン 一級 500mL 16000485	1,900	2,200	2397	2397									
89-0067-38	ワセリン(白色) CP 500g 22000255	2,400	2,500	-	-									
89-0067-47	酸化亜鉛 一級 500g 26000375	1,200	1,700	-	-									
8-9009-11	ドクターズツール 本体 LS-150HY	150,000	155,000			1561								
8-9399-01	採尿パック(女児用)1箱(50枚入) 49003	10,000	12,000			1905								
8-9917-01	スケルトンカート TS-SA	148,000	167,000			91								
8-9918-01	スケルトン救急カート TS-SE	160,000	181,000			941								
9-5702-31	グリーンハンガーラックACHLN ACHLN(スチール)	370,000	384,000	3154	3154									
9-5703-01	ステンレスロッカー SW-450	165,000	213,000	3156	3156			357						
9-5703-02	ステンレスロッカー SW-900	290,000	312,000	3156	3156			357						